

G 7264 C SCVi

Fully integrated dishwashers
with 3D MultiFlex tray for maximum convenience.



- Perfect results in less than one hour – QuickPowerWash
- Completely dry – Miele AutoOpen drying
- Fresh water dishwashers – as little as ?? water consumed in Automatic programme
- Very easy door opening and closing – ComfortClose
- Convenient, great results, perfect for everyday use – ExtraComfort C baskets

EAN: 4002516801436 / Material number: 12583240 /
Old Material Number: 21726462SG

| Available display languages | |
|--|--|
| Available display languages via MultiLingua | bahasa malaysia, deutsch, english (GB), [?][?], [?][?] [?][?] |
| Model | |
| Fully integrated dishwasher | • |
| 60 cm dishwasher | • |
| Design | |
| Control panel colour | Stainless Steel. |
| Control panel version | Fully integrated fascia |
| Control type | Programme selector buttons |
| Display | 1-line text display |
| Display colour | White |
| MultiLingua | • |
| Convenience | |
| Door closing aid | AutoClose |
| Operating noise dB(A) re 1 pW | 44 |
| Time left display | • |
| Delay start up to 24 hours | • |
| In-operation indicator light | optical and acoustic |
| Display language selection | • |
| Efficiency and sustainability | |
| Drying class | A |
| Water consumption in the ECO programme in l | 8,9 |
| Annual water consumption in the ECO programme in l | 2492 |
| Annual energy consumption in ECO programme in kWh | 192 |
| Number of place settings | 12 |
| EcoFeedback | • |
| EcoPower Technology | • |
| Proven hygiene | • |
| Hot water connection | • |
| Half load | • |
| Quality of results | |
| Fresh water dishwasher | • |
| AutoOpen drying | • |
| SensorDry | • |
| Active condensation drying | • |
| BrilliantGlassCare | • |
| Wash programmes | |
| QuickPowerWash | • |
| ECO | • |
| Automatic | • |
| ComfortWash 45 °C | • |
| Intensive 75 °C | • |
| PowerWash | • |
| ComfortWash+ 55 °C | • |
| Gentle | • |

G 7264 C SCVi

Fully integrated dishwashers

with 3D MultiFlex tray for maximum convenience.



EAN: 4002516801436 / Material number: 12583240 /

Old Material Number: 21726462SG

| | |
|--|---------------------|
| ExtraQuiet 40 dB(A) | • |
| Appliance care | • |
| Rinse out salt | • |
| Dishwashing options | |
| BottleClean | • |
| Quick | • |
| IntenseZone | • |
| Extra Clean | • |
| Extra dry | • |
| Basket design | |
| Cutlery loading | 3D MultiFlex tray C |
| Chopstick holders | • |
| FlexCare glass holder | 3 |
| FlexCare cup rack | 1 |
| Basket design | ExtraComfort C |
| MultiClip | • |
| FlexCare Glass & Bottle | • |
| Safety | |
| Waterproof system | • |
| Filter indicator light | • |
| Technical data | |
| Niche width minimal in mm | 600 |
| Niche width max in mm | 600 |
| Niche height minimal in mm | 805 |
| Niche height maximal in mm | 870 |
| Niche depth in mm | 550 |
| Appliance width in mm | 598 |
| Appliance height in mm | 805 |
| Appliance depth in mm | 550 |
| Depth with door open in cm | 116,5 |
| Net weight in kg | 48,0 |
| Total rated load in kW | 2,00 |
| Voltage in V | 230 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Electrical frequency standard | 50 |
| Length of water inlet hose in cm | 1,50 |
| Length of water drain hose in cm | 1,50 |
| Length of supply lead in m | 1,80 |
| Min. front panel weight in kg | 4,0 |
| Max. front panel weight in kg | 10,0 |
| [can be retrofitted by Service to min.] | 8,0 |
| [can be retrofitted by Service to max.] | 16,0 |
| Accessories included | |
| 1 x UltraTabs box (20 tabs) | • |
| Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price | • |

G 7264 C SCVi

Fully integrated dishwashers
with 3D MultiFlex tray for maximum convenience.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),