

G 7604 C SCi AutoDos  
Semi-integrated dishwasher  
43 dB | Cutlery tray | ExtraComfort C baskets | AutoDos | Hygiene 75°C



- Tested for the equivalent of 20 years' service life\*
- Convenient, great results, perfect for everyday use – ExtraComfort C baskets
- Convenient, efficient, sustainable – perfect results with automatic dispensing from PowerDisk
- More information options and modern domestic appliance networking – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Completely dry – Miele AutoOpen drying

\* During the development phase of the G 5000 and G 7000 dishwasher series, Miele tested models and core components in 5600 wash cycles (= 280 wash cycles per year over a period of 20 years) in various programmes. More at: [miele.com/20years](http://miele.com/20years)

EAN: 4002516801450 / Material number: 12583370 /  
Old Material Number: 21760457SG

General information	
Model identifier	G 7604 C SCi AutoDos
Manufacturer material number	12583370
EAN number	4002516801450
Marketing class	Platinum
Model	
Semi-integrated dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Stainless steel/CleanSteel
Control panel version	Straight fascia
Control type	Softkeys
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
Operating noise dB(A) re 1 pW	43
Time left display	•
Delay start up to 24 hours	•
In-operation indicator	volume control, acoustic, Display
Display language selection	•
Efficiency and sustainability	
Drying class	A
Water consumption in the Automatic programme in l from	6,0
Water consumption in the ECO programme in l	8,9
Annual water consumption in the ECO programme in l	2492
Annual energy consumption in ECO programme in kWh	192
Number of place settings	12
Noise emissions in dB(A)	43
FlexiTimer with EcoStart	•
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•

G 7604 C SCi AutoDos  
Semi-integrated dishwasher  
43 dB | Cutlery tray | ExtraComfort C baskets | AutoDos | Hygiene 75°C



EAN: 4002516801450 / Material number: 12583370 /  
Old Material Number: 21760457SG

Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•
Gentle	•
Hygiene	•
SolarSave	•
ExtraQuiet 38 dB(A)	•
Appliance care	•
Rinse out salt	•
<b>Dishwashing options</b>	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray C
Chopstick holders	•
FlexCare glass holder	3
FlexCare cup rack	1
Basket design	ExtraComfort C
MultiClip	•
FlexCare Glass & Bottle	•
<b>Safety</b>	
Waterproof system	•
Filter indicator light	•
Safety lock	•
System lock	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	570
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	570
Depth with door open in cm	116,5
Net weight in kg	49,2
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in m	1,50

G 7604 C SCi AutoDos  
 Semi-integrated dishwasher  
 43 dB | Cutlery tray | ExtraComfort C baskets | AutoDos | Hygiene 75°C



EAN: 4002516801450 / Material number: 12583370 /  
 Old Material Number: 21760457SG

Length of water drain hose in m	1,50
Length of supply lead in m	1,80
Min. front panel weight in kg	3,0
Max. front panel weight in kg	11,0
[can be retrofitted by Service to min.]	8,0
[can be retrofitted by Service to max.]	17,0

#### Accessories included

1 x PowerDisk	•
Voucher for 6 x PowerDisk	•


#### Available display languages

Available display languages via MultiLingua	☐☐, ☐☐☐☐, deutsch, english (GB), bahasa malaysia
---	--

G 7604 C SCi AutoDos

Semi-integrated dishwasher

43 dB | Cutlery tray | ExtraComfort C baskets | AutoDos | Hygiene 75°C



G7000, integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761)