

G 7654 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Cutlery tray with chopstick holder for maximum convenience – 3D MultiFlex
- More information options and modern domestic appliance networking – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Fresh water dishwashers – as little as ?? water consumed in Automatic programme
- Convenient, great results, perfect for everyday use – ExtraComfort C baskets
- Completely dry – Miele AutoOpen drying

EAN: 4002516801467 / Material number: 12583430 / Old Material Number: 21765462SG

Model	
Fully integrated dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Obsidian Black
Control panel version	Fully integrated fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Operating noise dB(A) re 1 pW	43
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	optical and acoustic, volume control
Display language selection	•
Efficiency and sustainability	
Drying class	A
Water consumption in the ECO programme in l	8,9
Annual water consumption in the ECO programme in l	2492
Annual energy consumption in ECO programme in kWh	192
Number of place settings	12
FlexiTimer with EcoStart	•
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Recirculation Turbothermic drying	•
BrilliantGlassCare	•
Wash programmes	
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•
Gentle	•
QuickPowerWash	•
Hygiene	•
SolarSave	•
ExtraQuiet 39 dB(A)	•
Appliance care	•

G 7654 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516801467 / Material number: 12583430 / Old Material Number: 21765462SG

Rinse out salt	•
Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray C
Chopstick holders	•
FlexCare glass holder	3
FlexCare cup rack	1
Basket design	ExtraComfort C
MultiClip	•
FlexCare Glass & Bottle	•
Safety	
Waterproof system	•
Filter indicator light	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	550
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	550
Depth with door open in cm	116,5
Net weight in kg	48,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Min. front panel weight in kg	4,0
Max. front panel weight in kg	11,0
[can be retrofitted by Service to min.]	7,0
[can be retrofitted by Service to max.]	14,0
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, deutsch, english, ,
Accessories included	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7654 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

- 1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
- 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),