

## G 7984 C SCVi AutoDos K2O

Fully integrated dishwashers

– the Miele all-rounder for handleless kitchen designs.



- More information options and modern domestic appliance networking – Miele@home
- Convenient, efficient, sustainable – perfect results with automatic dispensing
- Combining perfection in kitchen design with automatic opening – Knock2open
- Intuitive, fast and clear touch operation – M Touch display
- Maximum flexibility and premium basket design – MaxiComfort C basket design
- Cutlery tray with chopstick holder for maximum convenience – 3D MultiFlex

EAN: 4002516801474 / Material number: 12583480 / Old Material Number: 21798462SG

| Model  |                                      |
|--|--------------------------------------|
| Fully integrated dishwasher                        | •                                    |
| 60 cm dishwasher                                   | •                                    |
| Design   |                                      |
| Control panel colour                               | CleanSteel/Obsidian black            |
| Control panel version                              | Fully integrated fascia              |
| Control type                                       | Programme selector button            |
| Display  | M Touch Vi                           |
| Display colour                                     | White                                |
| MultiLingua  | •                                    |
| Convenience  |                                      |
| Networking with Miele@home                         | •                                    |
| Automatic dispensing with PowerDisk                | •                                    |
| Knock2open   | •                                    |
| Door closing aid                                   | AutoClose inkl. ComfortClose         |
| BrilliantLight                                     | •                                    |
| Operating noise dB(A) re 1 pW                      | 42                                   |
| Time left display                                  | •                                    |
| Delay start up to 24 hours                         | •                                    |
| In-operation indicator light                       | optical and acoustic, volume control |
| Add an item option                                 | •                                    |
| Display language selection                         | •                                    |
| Efficiency and sustainability                      |                                      |
| Drying class                                       | A                                    |
| Water consumption in the ECO programme in l        | 8,9                                  |
| Annual water consumption in the ECO programme in l | 2492                                 |
| Annual energy consumption in ECO programme in kWh  | 192                                  |
| Number of place settings                           | 12                                   |
| FlexiTimer with EcoStart                           | •                                    |
| EcoFeedback  | •                                    |
| EcoPower Technology                                | •                                    |
| Proven hygiene                                     | •                                    |
| Hot water connection                               | •                                    |
| Half load  | •                                    |
| Quality of results                                 |                                      |
| Fresh water dishwasher                             | •                                    |
| AutoOpen drying                                    | •                                    |
| SensorDry  | •                                    |
| Recirculation Turbothermic drying                  | •                                    |
| BrilliantGlassCare                                 | •                                    |
| Wash programmes                                    |                                      |
| ECO  | •                                    |
| Automatic  | •                                    |
| ComfortWash 45 °C                                  | •                                    |
| Intensive 75 °C                                    | •                                    |
| PowerWash  | •                                    |
| ComfortWash+ 55 °C                                 | •                                    |
| Gentle   | •                                    |

## G 7984 C SCVi AutoDos K2O

Fully integrated dishwashers

– the Miele all-rounder for handleless kitchen designs.



EAN: 4002516801474 / Material number: 12583480 / Old Material Number: 21798462SG

|   |                     |
|---|---------------------|
| QuickPowerWash                          | •                   |
| Hygiene                                 | •                   |
| SolarSave                               | •                   |
| ExtraQuiet 39 dB(A)                     | •                   |
| Pasta/Paella                            | •                   |
| Tall items 65°C                         | •                   |
| Appliance care                          | •                   |
| Rinse out salt                          | •                   |
| <b>Dishwashing options</b>              |                     |
| AutoDos                                 | •                   |
| BottleClean                             | •                   |
| Quick                                   | •                   |
| IntenseZone                             | •                   |
| Extra Clean                             | •                   |
| Extra dry                               | •                   |
| <b>Basket design</b>                    |                     |
| Cutlery loading                         | 3D MultiFlex tray C |
| Chopstick holders                       | •                   |
| FlexCare glass holder                   | 4                   |
| FlexCare cup rack                       | 1                   |
| Basket design                           | MaxiComfort C       |
| MultiClip                               | •                   |
| FlexCare Glass & Bottle                 | •                   |
| XL Assist                               | •                   |
| StrawClean                              | •                   |
| <b>Safety</b>                           |                     |
| Waterproof system                       | •                   |
| Filter indicator light                  | •                   |
| <b>Technical data</b>                   |                     |
| Niche width minimal in mm               | 600                 |
| Niche width max in mm                   | 600                 |
| Niche height minimal in mm              | 805                 |
| Niche height maximal in mm              | 870                 |
| Niche depth in mm                       | 550                 |
| Appliance width in mm                   | 598                 |
| Appliance height in mm                  | 805                 |
| Appliance depth in mm                   | 550                 |
| Depth with door open in cm              | 116,5               |
| Net weight in kg                        | 48,0                |
| Total rated load in kW                  | 2,00                |
| Voltage in V                            | 230                 |
| Fuse rating in A                        | 10                  |
| Number of phases                        | 1                   |
| Electrical frequency standard           | 50                  |
| Length of water inlet hose in cm        | 1,50                |
| Length of water drain hose in cm        | 1,50                |
| Length of supply lead in m              | 1,80                |
| Min. front panel weight in kg           | 4,0                 |
| Max. front panel weight in kg           | 11,0                |
| [can be retrofitted by Service to min.] | 7,0                 |
| [can be retrofitted by Service to max.] | 14,0                |

G 7984 C SCVi AutoDos K2O  
 Fully integrated dishwashers  
 – the Miele all-rounder for handleless kitchen designs.



EAN: 4002516801474 / Material number: 12583480 / Old Material Number: 21798462SG

Replacing lamps

Service

**Available display languages**

Available display languages via MultiLingua

bahasa malaysia, dansk, deutsch, english (AU), english (GB), english (US), español, français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portuguese, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, , , ,

**Accessories included**

1 x PowerDisk

•


Voucher for 6 x PowerDisk

•

## G 7984 C SCVi AutoDos K20

Fully integrated dishwashers

– the Miele all-rounder for handleless kitchen designs.



G7000, fully integrated dishwasher, 60cm (installation drawing)

- 1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
- 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),