

EVS 7010

Handleless built-in vacuum drawer, 14 cm high
for professional vacuum packing of food.




- Remains fresh for longer – storage and portioning of food
- Intense taste – marinating food
- Preparation of food for sous-vide cooking
- Easy handling – Touch controls and fully telescopic runners
- Opening the drawer couldn't be easier – Push2open

EAN: 4002516835257 / Material number: 12641390 /
Old Material Number: 30701061GB

General information	
Model identifier	EVS 7010
Manufacturer material number	12641390
EAN number	4002516835257
Construction type and design	
VitroLine	•
Colour	Pearl beige
ArtLine	•
Handleless	•
Appliance type and design	
Vacuum drawer	•
Programmes	
Vacuum seal	•
Convenience features	
Marinating food	•
Convenience features and range of applications	
Vacuum sealing food	•
Vacuum sealing liquids	•
Vacuum sealing containers	•
Extending the shelf life of food	•
Preparing food for sous-vide cooking	•
Marinating food	•
Dividing food into portions	•
Resealing original packaging	•
Resealing jars	•
User convenience	
Control panel with sensor controls	•
Fully telescopic runners	•
Control panel with symbols	•
Push2open	•
Vacuumping strength min. in steps	1
Max. vacuum settings	3
LED vacuum setting indicator	•
Vacuumping strength min. for external containers in steps	1
Max. vacuum settings for external containers	3
LED vacuum setting indicator	•
LED sealing duration indicator	•
Sealing duration settings	1 - 3
Stop function	•
Vacuum-sealing technology	
Stainless-steel vacuum chamber	•
Cleaning and care	
Flush control panel	•
Note regarding moisture removal from the vacuum pump	•
Interchangeable sealing bar	•
Safety	
Safety switch-off	•

EVS 7010

Handleless built-in vacuum drawer, 14 cm high
for professional vacuum packing of food.




EAN: 4002516835257 / Material number: 12641390 /
Old Material Number: 30701061GB


Technical data	
Appliance width in mm	595
Appliance height in mm	141
Capacity in l	8,0
Appliance depth in mm	570
Pump capacity in m ³ /h	4
Minimum bag size in mm	250
Total rated load in kW	0,32
Maximum bag size in mm	350
Voltage in V	230
Frequency in Hz	50-60
Fuse rating in A	10
Number of phases	1
Useable interior height in mm	80
Mains connection cable with mains plug	•
Length of mains connection cable in m	1,8
Accessories included	
Adapter for vacuum sealing containers	1
Vacuum sealing bag support	1
Vacuum sealing bags	•
Number of vacuum sealing bags 180 x 280 mm	50
Number of vacuum sealing bags 240 x 350 mm	50

EVS 7010

Handleless built-in vacuum drawer, 14 cm high
for professional vacuum packing of food.




Installation_DG_DGM_DGC_XL_ESW7x10_EVS7010, installation drawings




Side view_DG_DGM_ESW7x10_EVS7010 installation drawings


A) 22 mm glass, 23,3 mm stainless steel



Installation_DGC_XXL_ESW7x10_EVS7010 installation drawings




built-in ESW7x10 EVS7010, installation drawing




built-in EVS 7010 build-under, installation drawing

1) Countertop overhang ≤ 29mm



side view ESW7x10 EVS7010, installation drawing, GB, AU



installation EVS7010 installation drawing, GB, AU

1) Mains connection cable, L=2000 mm, 2) No connection in this area, 3) Ventilation cutout min. 180 cm²