

## PWM 935 [EL DV DD SOM]

Professional washing machine, electric heating  
for marine applications – freely programmable. 35 kg load size.



EAN: 4002516928539 / Material number: 12887790 /  
Old Material Number: 51935006SOM

### Construction type and version

Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Load ratio	1:9
Load in kg	35,0
Drum volume in l	320
Door opening [Ø] in mm	415
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Maintenance-free motor with frequency converter	•
Patented stainless steel honeycomb drum 2.0	•

### Application

Suitable for offshore use	•
Suitable for marine use	•

### Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	7,50
Specific energy consumption for cold water connection in kWh/kg	0,22
Specific water consumption for hot water connection in l/kg	7,50
Specific energy consumption for hot water connection in kWh/kg	0,06
Water consumption with cold water connection in l	262,5
Water consumption for cold water connection in Mops standard 60 °C programme in l	422,3
Energy consumption with cold water connection in kW	7,60
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	7,95
Programme duration in minutes with cold water connection	61
Water consumption with hot water connection in l	261,6
Water consumption for hot water connection in Mops standard 60 °C programme in l	427,3
Energy consumption with hot water connection in kW	2,16
Energy consumption for hot water connection in Mops standard 60 °C programme in kWh	2,59
Programme duration in minutes with cold water and hot water connection	49
Water consumption in ECO programme with cold water connection in l	242,0
Energy consumption in ECO programme with cold water	5,30
Programme duration in minutes with cold water connection in ECO programme	44
Water consumption in ECO programme with hot water connection in l	243,6

- Volume of the honeycomb drum 320 l, maximum load size 35.0 kg
- 19 % less water consumption and 40 % less energy consumption\*
- Short subsequent drying thanks to BoostSpin
- Ideal operation thanks to colour touch display – M Touch Pro Plus
- Connected for the future using LAN and WiFi

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

## PWM 935 [EL DV DD SOM]

Professional washing machine, electric heating  
for marine applications – freely programmable. 35 kg load size.



EAN: 4002516928539 / Material number: 12887790 /  
Old Material Number: 51935006SOM

Energy consumption in ECO programme with hot water	0,76
Programme duration in minutes with cold water and hot water connection in ECO programme	37
Programme running time in minutes for Mops standard 60 °C programme with cold water connection	59
Programme running time in minutes for Mops standard 60 °C programme with hot water connection	52
Residual moisture with cold rinse in %	51
Residual moisture with hot rinse in %	44
Residual moisture when processing cleaning cloths in %	14
Spin speed in rpm	1060
g factor	502
Tested operating hours	30000
<b>Control system</b>	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Customer-specific pre-configuration possible	•
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Language can be selected easily at any time	•
Option to enter weight prior to start of programme	•
<b>Dispensing</b>	
Detergent drawer	4 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3 AC 400V 50 HZ
Heater rating in kW	30,00
Total connected load in kW	31,60
Fuse rating in A	63
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 400V 60 HZ
Heater rating in kW	30,00
Total connected load in kW	31,60
Fuse rating in A	63
<b>Water connection/drainage</b>	
Cold water [number]	4 x 1/2" w/ 3/4" union
Hot water [number]	2 x 1/2" w/ 3/4" union
Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70
<b>Dimensions and weight</b>	
External dimensions, height in mm	1646
External dimensions, width in mm	1090
External dimensions, depth in mm	1275
External dimensions, gross height in mm	1793

## PWM 935 [EL DV DD SOM]

Professional washing machine, electric heating  
for marine applications – freely programmable. 35 kg load size.

EAN: 4002516928539 / Material number: 12887790 /  
Old Material Number: 51935006SOM

External dimensions, gross width in mm	1365
External dimensions, gross depth in mm	1425
Net weight in kg	665,0
Gross weight in kg	722
Maximum floor load in N	9540
<b>Emissions data</b>	
Emission sound pressure level in the workplace	71 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	6,10
<b>Features</b>	
Patented pre-spin	•
Cloth reprocessing	•
Imbalance monitoring	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
BoostSpin	•
Temperature monitoring	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Weighing plinth (optional)	•
Add laundry	•
Programme selection via colour frame	•
Efficient fast spin cycle	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•
<b>Capacities</b>	
Respirator masks [number]	26
Helmets [number]	10
Overalls [number]	6
Over jackets [number]	9
Chemical protection suits [number]	4
Synthetic duvets [number]	4
Synthetic pillows [number]	8
Down duvets [number]	4
Down pillows [number]	8
Cloths, 22 g [number]	800
Cotton mops, 40 cm / 190 g [number]	184
Cotton mops, 50 cm / 220 g [number]	159
Microfibre mops, 40 cm / 120 g [number]	292

## PWM 935 [EL DV DD SOM]

Professional washing machine, electric heating  
for marine applications – freely programmable. 35 kg load size.



EAN: 4002516928539 / Material number: 12887790 /

Old Material Number: 51935006SOM

Microfibre mops, 50 cm / 170 g [number]	206
---	-----

Summer horse blankets [number]	5
--------------------------------	---

### Standards, test certificates and symbols

CE	•
----	---

VDE-EMC	•
---------	---

VDE	•
-----	---

Splash-proof safety rating IPX4	•
---------------------------------	---

WEEE	•
------	---

Complies with Machinery Directive 2006/42/EC	•
--	---