

KMDA 7473-1 FL Silence

Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area



- The quietest TwoInOne from Miele – Silence motor
- Ample space – 4 large cooking zones incl. 2 Flex zones
- Automatic fan power regulation – Con@ctivity
- Compact control using the numerical display – ComfortSelect Plus
- Flexible installation – Plug & Play, ducted recirculation or vented system

EAN: 4002516974680 / Material number: 12968760 /
Old Material Number: 26747375GB

General information	
Model identifier	KMDA 7473-1 FL Silence
Manufacturer material number	12968760
EAN number	4002516974680
Class	Gold
Construction type	
Induction hob with integrated vapour extraction	•
Operating modes	
Exhaust air guided with optional accessories	DFK-xxxx,DMK 150-1
Recirculation air guided with optional accessories	DFK-xxxx,DUU 1500,DUU 600
Recirculation air guided with optional accessories	Can be retrofitted
Unguided recirculation air (Plug&Play installation)	•
Design	
Elegant glass ceramic surface	•
Frameless – surface-mounted	•
Flush	•
Ceramic surface colour	Black
Flush fit extractor	•
Colour of cover grille	Stainless steel
Cooking zone details	
Number of cooking zones	4
Number of cooking areas	2
Maximum number of pans	4
PowerFlex cooking zones	
No.	4
Type	Flex cooking zone
Size in mm	Ø 110-210
Max. rating in W	2100
Max. Booster power rating in W	3000
1st cooking zone/cooking area	
Position	Left
Type	Flex cooking area
Size in mm	210x420
Max. rating in W	3000
Max. Booster power rating in W	3700
2nd cooking zone/cooking area	
Position	right
Type	Flex cooking zone
Size in mm	210x420
Max. rating in W	3000
Max. Booster power rating in W	3700
User convenience	
Networking with Miele@home	•
Con@ctivity	•
Digital power level display	•
Operation via sensor controls	ComfortSelect Plus
Display colour	Yellow

KMDA 7473-1 FL Silence

Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area



EAN: 4002516974680 / Material number: 12968760 /

Old Material Number: 26747375GB

Keeping warm plus	•
Permanent pan recognition	•
Run-on time 5/15 min.	•
Active charcoal filter saturation indicator	•
Stop & Go function	•
Wipe protection	•
Recall function	•
Grease filter saturation indicator	•
Minute minder	•
Safety switch-off	•
Auto heat-up	•
Keeping warm	•
Individual setting options (e.g. buzzers)	•
Easy-to-clean canopy interior – CleanCover	•

Efficiency and sustainability

Energy efficiency class (A+++ – D)	A+
Power rating in off mode in W	0,5
Power rating in standby mode in W	0,8
Power rating in networked standby in W	2,0
ECO motor	•
Time until automatic switch to standby in min	10
Annual energy consumption in kWh/year	31,3
Time until automatic switch to networked standby in min	10
Silence motor	•
Time until automatic switch to off mode in min	10
Fluid dynamic efficiency class	A
Lighting efficiency class	NA
Grease filtering efficiency class	A

Cleaning and care

Easy to clean ceramic glass	•
-----------------------------	---

Filter system

Number of dishwasher-safe metal grease filters (10-ply)	1
---	---

Exhaust air

Air throughput at min. level (m³/h) according to EN 61591	205
Air throughput at max. level (m³/h) according to EN 61591	533
Air throughput in Intensive level (m³/h) according to EN 61591	606
Sound power at min. level (dB(A) re 1 pW) according to EN 60704-3	41
Sound power at max. level (dB(A) re 1 pW) according to EN 60704-3	64
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	68
Sound pressure at min. level (dB(A) re 20 µPa) according to EN 60704-2-13	28,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	68,0
Sound pressure at max. level (dB(A) re 20 µPa) according to EN 60704-2-13	51,0

KMDA 7473-1 FL Silence

Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area

EAN: 4002516974680 / Material number: 12968760 /

Old Material Number: 26747375GB

Noise pressure level in Intensive level (dB(A) re 20 µPa) according to EN 60704-2-13	54,0
--	------

Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	54,0
---	------

Recirculation

Air throughput at min. level (m³/h) according to EN 61591	160
---	-----

Air throughput at max. level (m³/h) according to EN 61591	475
---	-----

Air throughput in Booster level (m³/h) according to EN 61591	510
--	-----

Sound power at min. level (dB(A) re 1 pW) according to EN 60704-3	46,0
---	------

Sound power at max. level (dB(A) re 1 pW) according to EN 60704-3	68,0
---	------

Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	70,0
---	------

Sound pressure at min. level (dB(A) re 20 µPa) according to EN 60704-2-13	33,0
---	------

Sound pressure at max. level (dB(A) re 20 µPa) according to EN 60704-2-13	55,0
---	------

Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	57,0
---	------

Safety

Safety switch-off	•
-------------------	---

Lock function	•
---------------	---

System lock	•
-------------	---

Integrated cooling fan	•
------------------------	---

Overheating protection	•
------------------------	---

Technical data

Dimensions in mm (width)	800
--------------------------	-----

Dimensions in mm (height)	200
---------------------------	-----

Dimensions in mm (depth)	520
--------------------------	-----

Casing height incl. connection box in mm	200
--	-----

Number of phases	3
------------------	---

Cutout dimensions in mm (width) with surface-mounted installation	780 mm
---	--------

Cutout dimensions in mm (depth) with surface-mounted installation	500 mm
---	--------

Internal cutout dimensions in mm (width) with flush installation	780
--	-----

Internal cutout dimensions in mm (depth) with flush installation	500
--	-----

Weight in kg	15
--------------	----

External cutout dimensions in mm (width) with flush installation	804
--	-----

External cutout dimensions in mm (depth) with flush installation	524
--	-----

Total rated load in kW	7,50
------------------------	------

Voltage in V	230
--------------	-----

Frequency in Hz	50-60
-----------------	-------

Length of supply lead in m	1,6
----------------------------	-----

Neutral conductor	Yes
-------------------	-----

KMDA 7473-1 FL Silence
Induction hob with integrated vapour extraction
800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area




EAN: 4002516974680 / Material number: 12968760 /
Old Material Number: 26747375GB

Accessories included	
Mains cable	Yes
Active charcoal filter DKF 35-P	•
Plug&Play adapter	•

KMDA 7473-1 FL Silence


Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – flush

1) Front, 2) removable drip tray, 3) cleaning flap, 4) Mains connection box with mains connection cable, L = 1600 mm, 5) Step milling natural stone worktop, 6) Wooden strip 12 mm (not included in delivery), 7) Worktop thickness, Exhaust air and guided recirculation mode: ≥ 10 mm, Plug&play operation: ≥ 10 mm – ≤ 40 mm




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL


1) Front, 2) Removable drip tray, 3) Cleaning flap, 4) Mains connection box with mains connection cable, L = 1600 mm, 5) Worktop thickness, Exhaust air and guided recirculation mode: ≥ 10 mm, Plug&Play operation: ≥ 10 mm – ≤ 40 mm




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR, Exhaust air



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR, Air circulation



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR, Plug&Play




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view flush, Plug&Play

② When routing the exhaust air between the cabinet wall and an adjacent room wall or an adjacent piece of furniture, a minimum distance of 25 mm must be observed., ② The removable collection tray and the cleaning flap must be accessible after installation., ② The cross-section of the ventilation opening must be at least 425 cm²., ② Distance from the front of the lower box to the end of the plug & play adapter

KMDA 7473-1 FL Silence


Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view lying on top, Plug&Play

When routing the exhaust air between the cabinet wall and an adjacent room wall or an adjacent piece of furniture, a minimum distance of 25 mm must be observed. The removable collection tray and the cleaning flap must be accessible after installation. The cross-section of the vent opening must be at least 425 cm². Distance from the front of the lower box to the end of the plug & play adapter




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view flush+X, Plug&Play

When routing the exhaust air between the cabinet wall and an adjacent room wall or an adjacent piece of furniture, a minimum distance of 25 mm must be observed. If the carcass rear wall is > 555 mm from the worktop front, the Plug&Play adapter must be extended with a supplementary set from Miele. The removable drip tray and the cleaning flap must be accessible after installation. The cross-section of the vent opening must be at least 425 cm². Distance from the front of the lower box to the end of the plug & play adapter, x Dimension by which the worktop depth is greater than 600 mm.




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view lying on top+X, Plug&Play

When routing the exhaust air between the cabinet wall and an adjacent room wall or an adjacent piece of furniture, a minimum distance of 25 mm must be observed. If the carcass rear wall is > 555 mm from the worktop front, the Plug&Play adapter must be extended with a supplementary set from Miele. The removable drip tray and the cleaning flap must be accessible after installation. The cross-section of the vent opening must be at least 425 cm². Distance from the front of the lower box to the end of the plug & play adapter, x Dimension by which the worktop depth is greater than 600 mm.




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view flush+X

The rear wall of the cabinet must be removable for servicing. A minimum distance of 110 mm must be maintained for routing the exhaust air duct between the cabinet wall and an adjacent room wall or furniture. The removable collection tray and the cleaning flap must be accessible after installation. x Dimension by which the worktop depth is greater than 600 mm.



KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view flush

The rear wall of the cabinet must be removable for servicing. A minimum distance of 110 mm must be maintained for routing the exhaust air duct between the cabinet wall and an adjacent room wall or furniture. The removable collection tray and the cleaning flap must be accessible after installation.




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view lying on top

The rear wall of the cabinet must be removable for servicing. A minimum distance of 110 mm must be maintained for routing the exhaust air duct between the cabinet wall and an adjacent room wall or furniture. The removable collection tray and the cleaning flap must be accessible after installation.

KMDA 7473-1 FL Silence


Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area




KMDA7272-1FL, KMDA7473-1FL, KMDA7272FL, KMDA7473FL – Side view lying on top+X

[2] The rear wall of the cabinet must be removable for servicing. A minimum distance of 110 mm must be maintained for routing the exhaust air duct between the cabinet wall and an adjacent room wall or furniture. [2] The removable collection tray and the cleaning flap must be accessible after installation., , x Dimension by which the worktop depth is greater than 600 mm.




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 1 Basis

1) DFK-AK 90, 2) DFK-R 1000




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 2 Basis

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 3 Basis

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-BH 90



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 4 Circulating air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-BH 90, 5) DFK-V, 6) DUU 1500, , The minimum width of the cabinet is 1350 mm.




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 5 Circulating air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-BH 90, 5) DFK-V, 6) DUU 1500, , The minimum width of the cabinet is 1350 mm.

KMDA 7473-1 FL Silence


Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 6 Circulating air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-V, 5) DUU 1500, , The minimum depth of the cabinet is 935 mm.




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 13 Circulating air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-BH 90, 5) DFK-V, 6) DUU 1500, , The minimum width of the cabinet is 1125 mm.




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 14 Circulating air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BV 90, 4) DFK-BH 90, 5) DFK-V, 6) DUU 1500, , The minimum width of the cabinet is 900 mm.




KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 9 Exhaust air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BH 90, 4) DFK-A, 5) DMK 150-1



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 10 Exhaust air

1) DFK-AK 90, 2) DFK-R 1000, 3) DMK 150-1






KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 11 Exhaust air

1) DMK 150-1, 2) Flex hose

KMDA 7473-1 FL Silence

Induction hob with integrated vapour extraction

800 mm | Extraction and recirculation | SilenceMotor | Flex cooking area






KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR – Installation variant 12 Exhaust air

1) DFK-AK 90, 2) DFK-R 1000, 3) DFK-BH 90, 4) DFK-A, 5) DMK 150-1

Installation plan DVS150PP



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR, Exhaust air



KMDA7272-1FL/FR, KMDA7473-1FL/FR, KMDA7272FL/FR, KMDA7473FL/FR, Air circulation

KMDA7272-1FL/FR, KMDA7473-1FL/FR – surface installation, 21 cm, drilling template

KMDA7272-1FL, KMDA7473-1FL – flush installation, drilling template, Installation depth 21 cm



KMDA7272-1FL, KMDA7473-1FL – flush installation, drilling template, Installation depth 20 cm

KMDA7272-1FL/FR, KMDA7473-1FL/FR – surface installation, drilling template