

E 414

Mobile unit

for the optimum loading of narrow necked glassware.



- equipped with 37 injector nozzles
- Equipped with connection for hot air drying
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002511116733 / Material number: 03810190 / Old Material Number: 69541401D

Product category	
Washer-disinfectors, laboratory	•
Machine affiliation	
PG 8535	•
PG 8536	•
Product category	
Mobile unit with connection for hot-air drying	•
Mobile unit for narrow-necked glassware	•
Product properties	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Area of application	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-necked glassware [number]	37
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	502
External dimensions, net width in mm	535
External dimensions, net depth in mm	517
External dimensions, gross height in mm	160
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	545
Net weight in kg	6.10
Gross weight in kg	7.10
Companion pack	
ID 90, injector nozzle, Ø 2.5 mm, length 90 mm [number]	4
ID 110, injector nozzle, Ø 2.5 mm, length 110 mm [number]	3
ID 140, injector nozzle, Ø 4 mm, length 140 mm [number]	5
ID 160, injector nozzle, Ø 4 mm, length 160 mm [number]	5
ID 180, injector nozzle, Ø 4 mm, length 180 mm [number]	5
ID 200, injector nozzle, Ø 6 mm, length 200 mm [number]	5
ID 220, injector nozzle, Ø 6 mm, length 220 mm [number]	5
ID 220, injector nozzle, Ø 6 mm, length 240 mm [number]	5
Rinse nozzle for powder dispenser [number]	1