

E 402  
Insert  
for optimum loading of up to 44 watch glasses.



- Suitable for 44 watch glasses Ø 80 – 125 mm
- Equipped with 23 bars spaced 15 mm

EAN: 4002511116627 / Material number: 03830420 / Old Material Number: 69540201D

<b>Product classification</b>	
Washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
PG 8527	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 8505	•
<b>Product category</b>	
Insert/module for watch glasses	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
Distance between rails in mm	15
<b>Area of application</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Watch glasses [number]	44
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	53
External dimensions, net width in mm	200
External dimensions, net depth in mm	445
External dimensions, gross height in mm	80
External dimensions, gross width in mm	220
External dimensions, gross depth in mm	450
Net weight in kg	0.92
Gross weight in kg	1.14