


E 940

Mobile unit

for the optimum loading of narrow necked glassware on 2 levels.



- The mobile injector unit can also be used without the upper level
- Magnetic strip for automatic mobile unit recognition
- Lower level equipped with a total of 15 nozzles with clips

EAN: 4002512145473 / Material number: 04607630 / Old Material Number: 69594001D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PG 8527	•
Product category	
Mobile unit for narrow-necked glassware	•
Product properties	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Area of application	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-necked glassware [number]	115
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in mm	565
External dimensions, net width in mm	640
External dimensions, net depth in mm	790
External dimensions, gross height in mm	760
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1200
Net weight in kg	35.00
Gross weight in kg	45.00
Companion pack	
Magnetic strip for automatic mobile unit recognition (incl. magnets) [number]	1