

E 815

Insert

For the optimum loading of glasses.



- Suitable for lower baskets U 890 and APFD 220
- For 10 tall beer glasses
- Rail height 240 mm, distance between rails 95 mm

EAN: 4002512259446 / Material number: 05018670 / Old Material Number: 67581501D

<b>Product category</b>	
Fresh-water dishwashers	•
<b>Machine affiliation</b>	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
<b>Product category</b>	
Insert for glassware	•
<b>Product properties</b>	
Material	Wire, rilsan-coated
Colour	White
Distance between rails in mm	95
Rail height in mm	240
For use in lower basket	U 890
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0

E 815

Insert

For the optimum loading of glasses.



EAN: 4002512259446 / Material number: 05018670 / Old Material Number: 67581501D

Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	252
External dimensions, net width in mm	220
External dimensions, net depth in mm	513
External dimensions, gross height in mm	250
External dimensions, gross width in mm	230
External dimensions, gross depth in mm	505
Net weight in kg	1.59
Gross weight in kg	1.99