


E 752

Module

for the optimum loading of narrow necked glassware 100 - 1,000 ml.



- With 12 nozzles (E 351) 4 x 160 mm with clips (E 353)
- With 13 nozzles (E 352) 6 x 220 mm with clips (E 354)

EAN: 4002513197471 / Material number: 05647640 / Old Material Number: 69575201D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
G 7826	•
<b>Product category</b>	
Insert/module for narrow-necked glassware	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of pipettes/phials	•
<b>Capacity</b>	
Narrow-necked glassware [number]	25
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	260
External dimensions, net width in mm	492
External dimensions, net depth in mm	496
External dimensions, gross height in mm	170
External dimensions, gross width in mm	530
External dimensions, gross depth in mm	560
Net weight in kg	9.70
Gross weight in kg	10.00