


UC 30-90/70-78

Box plinth

to raise the machine, 70 cm deep, 90 cm wide.



- Suitable for all machines, width 90, depth 70 cm
- Can be screwed onto the appliance

EAN: 4002513347807 / Material number: 05818100 / Old Material Number: 69379009D

| | |
|---|-----------------|
| Product classification | |
| Washer-disinfectors, laboratory | • |
| Washer-disinfectors, medical | • |
| Machine affiliation | |
| PG 8535 | • |
| Product category | |
| Plinth/base | • |
| Product properties | |
| Material | Stainless steel |
| Colour | Stainless Steel |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in mm | 300 |
| External dimensions, net width in mm | 900 |
| External dimensions, net depth in mm | 700 |
| External dimensions, gross height in mm | 370 |
| External dimensions, gross width in mm | 1000 |
| External dimensions, gross depth in mm | 730 |
| Net weight in kg | 13.20 |
| Gross weight in kg | 14.40 |