

E 741/1

Mobile unit

for the optimum loading of modules on 1 - 4 levels.



- Depending on size of the wash items up to 3 modules can be used
- Coupling of the mobile unit to the water and drying air supply
- The vertical clearance for the individual levels is different

EAN: 4002513512267 / Material number: 06070360 / Old Material Number: 69574102D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
G 7825	•
G 7826	•
Product category	
Other mobile units	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
Area of application	
Reprocessing of laboratory glassware	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	680
External dimensions, net width in mm	530
External dimensions, net depth in mm	600
External dimensions, gross height in mm	550
External dimensions, gross width in mm	640
External dimensions, gross depth in mm	650
Net weight in kg	12.00
Gross weight in kg	12.80