

## APWM 004

Connection box for dosing units

With connectors for a maximum of six dispenser pumps.



- Simple connection of liquid dispenser and siphon
- For simple wall mounting
- No need to open the lid of the machine
- Suitable for DOS MC dispenser pumps

EAN: 4002514507804 / Material number: 07304030 / Old Material Number: 59507001D

Product classification	
Washing machines	•
Machine/accessory category	
PW 413 Mop Star 130	•
PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5104 MOPSTAR 100	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 9055	•
PW 9065	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Dispenser system	•
Product properties	
Electrical connection	----
Material	Plastic
Colour	Grey
Dimensions and weight	
External dimensions, net height in mm	180
External dimensions, net width in mm	250
External dimensions, net depth in mm	90
External dimensions, gross height in mm	260
External dimensions, gross width in mm	285
External dimensions, gross depth in mm	200
Net weight [kg]	1.81
Gross weight in kg	2.27

APWM 004

Connection box for dosing units

With connectors for a maximum of six dispenser pumps.