

E 327/1

Mobile unit

for the optimum loading of 4 DIN mesh trays.



- Suitable for 4 DIN mesh trays on 2 levels
- Magnet for use with spray arm sensors for PG 8535, PG 8536
- With integrated magnetic spray arm
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002514556239 / Material number: 07333100 / Old Material Number: 69532702D

<b>Product category</b>	
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8535	•
PG 8536	•
<b>Product category</b>	
Mobile unit for mesh trays	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of surgical instruments	•
<b>Capacity</b>	
DIN mesh trays [number]	4
SPRI mesh trays [number]	2
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	410
External dimensions, net width in mm	530
External dimensions, net depth in mm	570
External dimensions, gross height in mm	420
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	595
Net weight in kg	2.40
Gross weight in kg	3.30