

## PT 7186 Vario [EL]

Vented dryer, electrically heated

with shortest programme running time of 37 min for a high laundry throughput.



- Drum volume 180.00 l, load size 8.0 kg
- Large programme variety – application-specific drying programmes
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002514674810 / Material number: 07553350 / Old Material Number: 52718642GB

| Construction type and design                          |                              |
|---|------------------------------|
| Construction type                                     | Front loader                 |
| Range   | Octoplus                     |
| Front   | Stainless steel              |
| Load in kg  | 8.0                          |
| Load ratio  | 1:22,5                       |
| Drum volume in l                                      | 180.00                       |
| Drying system   | Exhaust air                  |
| Door opening [Ø] in mm                                | 440                          |
| Door opening angle in degrees                         | 180                          |
| Door hinge  | left                         |
| Stainless steel honeycomb drum                        | Yes                          |
| Application   |                              |
| Suitable for the hotel and catering industry          | •                            |
| Suitable for retirement and care homes                | •                            |
| Suitable for facility management                      | •                            |
| Suitable for laundrettes                              | •                            |
| Suitable for residential homes and apartments         | •                            |
| Suitable for dry cleaners                             | •                            |
| Suitable for commercial laundries                     | •                            |
| Suitable for small businesses                         | •                            |
| Suitable for fire brigades and rescue services        | •                            |
| Suitable for studs, riding schools and stables        | •                            |
| Suitable for universities, nurseries, and schools     | •                            |
| Suitable for hospitals                                | •                            |
| Suitable for camp sites                               | •                            |
| Suitable for sports clubs                             | •                            |
| Suitable for beauty salons, spas, and fitness centres | •                            |
| Suitable for doctors' and dentists' practices         | •                            |
| Performance data                                      |                              |
| Maximum evaporation capacity in l/hour                | 8.10                         |
| Programme duration in min.                            | 37                           |
| Controls  |                              |
| Control system  | Profitronic L Vario          |
| Programmability                                       | programmable                 |
| User interface  | Residual moisture controlled |
| Max. delay start in h                                 | 24                           |
| Time left display                                     | •                            |
| Programme sequence indicator                          | •                            |
| Selectable display languages                          | •                            |
| Standard/target grp programmes                        |                              |
| Basic programmes                                      | •                            |
| Programmes for facility management                    | •                            |
| Programmes for dry cleaners                           | •                            |
| Programmes for fire brigades and rescue services      | •                            |
| Programmes for studs, riding schools, and stables     | •                            |
| Programmes for domestic use                           | •                            |
| Standard electrical connection                        |                              |
| Heating type  | Electric                     |

## PT 7186 Vario [EL]

Vented dryer, electrically heated

with shortest programme running time of 37 min for a high laundry throughput.



EAN: 4002514674810 / Material number: 07553350 / Old Material Number: 52718642GB

|  |                     |
|--|---------------------|
| Electrical connection                          | AC 230-240V 50HZ    |
| Electric heater rating in kW                   | 5.22-5.68           |
| Total connected load in kW                     | 5.78-6.24           |
| Fuse rating in A                               | 25                  |
| <b>Dimensions and weight</b>                   |                     |
| External dimensions, height in mm              | 1020                |
| External dimensions, width in mm               | 700                 |
| External dimensions, depth in mm               | 763                 |
| External dimensions, gross height in mm        | 1215                |
| External dimensions, gross width in mm         | 760                 |
| External dimensions, gross depth in mm         | 820                 |
| Net weight in kg                               | 77.0                |
| Gross weight in kg                             | 88                  |
| Maximum floor loading in N                     | 1000                |
| <b>Emissions data</b>                          |                     |
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h         | 1.62                |
| <b>Features</b>                                |                     |
| Intelligent drum reversal                      | •                   |
| Axial airflow                                  | •                   |
| Large-surface filter                           | •                   |
| PerfectDry                                     | •                   |
| SoftLift drum ribs                             | •                   |
| Low temperature function                       | •                   |
| Communication slot                             | •                   |
| Drying basket (optional)                       | •                   |
| Machine-independent accessories                | •                   |
| <b>Connection options</b>                      |                     |
| Payment system                                 | •                   |
| Serial interface RS 232 (optional)             | •                   |
| Optical interface for service access           | •                   |
| Peak load cut-out/energy management (optional) | •                   |
| <b>Capacities</b>                              |                     |
| Respirator masks [number]                      | 4                   |
| Overalls [number]                              | 1                   |
| Over jackets [number]                          | 1-2                 |
| Synthetic duvets [number]                      | 1                   |
| Synthetic pillows [number]                     | 1-2                 |
| Down pillows [number]                          | 1-2                 |
| Cloths, 22 g [number]                          | 182                 |
| Cotton mops, 40 cm [number]                    | 42                  |
| Cotton mops, 50 cm [number]                    | 36                  |
| Microfibre mops, 40 cm [number]                | 66                  |
| Microfibre mops, 50 cm [number]                | 47                  |
| Summer horse blankets [number]                 | 1-2                 |
| <b>Standards, certs, symbols</b>               |                     |
| CE   | •                   |
| VDE  | •                   |
| Splash-proof safety rating IPX4                | •                   |
| WEEE   | •                   |
| Complies with Machinery Directive 2006/42/EC   | •                   |