

E 735/2

Mobile unit

for the optimum loading of instruments on 3 levels.



- Equipped with 2 integrated spray arms
- The loading areas for the individual levels are different
- Magnetic strip for mobile unit recognition (without magnets ML)

EAN: 4002514816388 / Material number: 07765710 / Old Material Number: 69573503D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
G 7825	•
G 7826	•
<b>Product category</b>	
Mobile unit for inserts	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Capacity</b>	
DIN mesh trays [number]	6
SPRI mesh trays [number]	3
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	552
External dimensions, net width in mm	530
External dimensions, net depth in mm	600
External dimensions, gross height in mm	650
External dimensions, gross width in mm	550
External dimensions, gross depth in mm	640
Net weight in kg	10.80
Gross weight in kg	12.80
<b>Companion pack</b>	
Magnetic strip for automatic mobile unit recognition (without magnets) [number]	1