


KM 3010
Gas hob
with 4 burners




- Simple controls -single-handed operation via rotary dial control
- Elegant design – 626 mm wide gas on glass hob
- Versatile – 4 burners
- Extremely safe – GasStop function
- Easy cleaning – dishwasher-safe ComfortClean pot rests

EAN: 4002515055830 / Material number: 09101190 / Old Material Number: 26301050GB

Heating type	
Heating type	Gas
Construction type	
Independent of cooker	•
Design	
Ceramic surface colour	Black
Cast iron pot rests (matt black enamelled)	•
Miele logo embossed in stainless steel	•
Cooking zone details	
Number of cooking zones	4
Gas burner power rating	
Small burner in kW	1.00
Medium burner in kW	1.70
Large burner in kW	2.70
1st cooking zone/cooking area	
Position	front left
Type	High-speed burner
2nd cooking zone/cooking area	
Position	rear left
Type	Economy burner
3rd cooking zone/cooking area	
Position	rear right
Type	Standard burner
4th cooking zone/cooking area	
Position	front right
Type	Standard burner
User convenience	
Operation via knobs	•
Electronic ignition with single-hand operation	•
Cleaning and care	
Dishwasher-proof pot rests	•
Safety	
GasStop	•
GasStop & ReStart	•
Technical data	
Dimensions (H x W x D) in mm	54 x 626 x 526
Dimensions in mm (width)	626
Dimensions in mm (height)	54
Dimensions in mm (depth)	526
Cutout dimensions in mm (width) with surface-mounted installation	600
Cutout dimensions in mm (depth) with surface-mounted installation	500
Casing height incl. connection box in mm	63
Weight in kg	17
Total rated load in kW	7.10
Length of supply lead in m	1.4
Position of gas connection	Hinten links
Voltage in V	220-240
Frequency in Hz	50-60

KM 3010
Gas hob
with 4 burners



EAN: 4002515055830 / Material number: 09101190 / Old Material Number: 26301050GB

Accessories included	
Mains cable	No
Jets for liquid gas	•

