

## APH 110 Net500

### Segosoft network converter

for connection of machines with serial interface for a network.



- Converts serial data (RS 232) to network protocol (TCP/IP)
- Galvanic separation of all connections incl. surge protection
- Power over Ethernet (PoE) enabled
- For use with Segosoft Miele Edition
- Scope of delivery: plug-in power unit (1.4 m)

EAN: 4002515388464 / Material number: 09687440 / Old Material Number: 68815902D

Product classification	
Washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
Thermal disinfectors	•
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
Small sterilisers	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
G 7831	•
PS 1201 B	•
PS 1201 B EXCELLENCE	•
PS 1202 B	•
PWD 8541	•
PWD 8545	•
PWD 8546	•
PWD 8549	•
PWD 8531	•
PWD 8532	•
PLW 6011	•
PLW 6111	•
PWD 6121	•
PWD 6122	•
Product category	
Process documentation/operating documentation/communication	•
Product properties	
Colour	Blue
Area of application	
Reprocessing of pipettes/phials	•
Reprocessing of laboratory glassware	•
Reprocessing of slides	•
Reprocessing of butyrometers	•
Reprocessing of pharmacy/infusion bottles	•
Reprocessing of anaesthetic instruments	•
Reprocessing of MIS instruments	•
Reprocessing of ophthalmology instruments	•
Reprocessing of robotic instruments	•
Reprocessing of GYN instruments	•
Reprocessing of ENT instruments	•
Reprocessing of dental instruments	•
Reprocessing of theatre shoes	•
Reprocessing of basins	•
Reprocessing of kidney dishes	•
Reprocessing of baby bottles	•
Reprocessing of surgical instruments	•
Reprocessing of lumened instruments	•

APH 110 Net500  
 Segosoft network converter  
 for connection of machines with serial interface for a network.



EAN: 4002515388464 / Material number: 09687440 / Old Material Number: 68815902D

Reprocessing of orthopaedic surgery instruments	•
Reprocessing of intramedullary nails/bone marrow drills	•
Reprocessing of trays	•
Reprocessing of mesh trays	•
Reprocessing of measuring cylinders	•
Reprocessing of containers, e.g. soda lime containers	•
Reprocessing of different utensils	•
<b>Standard electrical connection</b>	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	100
Frequency in Hz	50-60
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	90
External dimensions, net width in mm	109
External dimensions, net depth in mm	31
External dimensions, gross height in mm	50
External dimensions, gross width in mm	155
External dimensions, gross depth in mm	235
Net weight in kg	0.32
Gross weight in kg	0.46
<b>Standards, certs, symbols</b>	
CE	•