

E 812

Use

For the optimum loading of glasses.



- Suitable for upper basket O 891 and O 892
- For 7 glasses with a diameter of max. 60 mm.

EAN: 4002515387672 / Material number: 09742240 / Old Material Number: 67581201D

<b>Product category</b>	
Fresh-water dishwashers	•
<b>Machine affiliation</b>	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
<b>Product category</b>	
Insert for glassware	•
<b>Product properties</b>	
Material	Wire, rilsan-coated
Colour	White
For use in upper basket	O 891, O 892
<b>Capacity</b>	
Glasses up to max. Ø 60 mm [number]	7
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0

E 812

Use

For the optimum loading of glasses.

EAN: 4002515387672 / Material number: 09742240 / Old Material Number: 67581201D



Dimensions and weight	
External dimensions, net height in mm	143
External dimensions, net width in mm	230
External dimensions, net depth in mm	467
External dimensions, gross height in mm	32
External dimensions, gross width in mm	615
External dimensions, gross depth in mm	50
Net weight in kg	0.30
Gross weight in kg	0.51