

PG 8504 [AD] Laboratory dishwasher with AD-water supply.

- Performance/cycle, e.g. 64 narrow-necked/laboratory glasses w/ injector nozzles
- Efficient use of resources – variable speed heater pump
- Dispense process chemicals easily: Powder dispenser in the door
- With DI water connection – final rinse with DI water

EAN: 4002515565261 / Material number: 10096780 / Old Material Number: 62850421GB

Construction type and version	
Construction type	Freestanding, can be built-under, slimline
Casing	Stainless steel
Can be built-under	•
Electric door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•
Application	
Suitable for laboratories	•
Capacity	
Narrow-necked glassware per cycle [number]	64
Performance data	
Circulation pump, Q _{max} in l/min	500
Wash cabinet usable capacity in l	145.00
Tested operating hours	15000
Maximum final rinse temperature in °C	70
Control system	
Control type	TouchControl
Programme selection	Touch on MSetal
Direct-access pushbuttons	•
Max. delay start in h	24
Programmability	programmable
Programmes [number]	6
Free programme positions [number]	2
Automatic programme restart	•
Time left display	•
Programme sequence display	•
Selectable display languages	•
Standard electrical connection	
Electrical connection	AC 230V 50HZ
Electric heater rating in kW	1.70
Total rated load in kW	2.40
Fuse rating in A	13
Length of mains connection cable in m	1.90
Water connection/drainage	
Cold water [number]	1
Required flow pressure in kPa	200-1000
DI water [number]	1
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10.70
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system
Dimensions and weight	
Net weight in kg	72
Dimensions and weight	
External dimensions, net height in mm	835
External dimensions, net width in mm	600
External dimensions, net depth in mm	600

PG 8504 [AD]
Laboratory dishwasher
with AD-water supply.

EAN: 4002515565261 / Material number: 10096780 / Old Material Number: 62850421GB

External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Wash cabinet, depth of upper basket in mm	474
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	79
Maximum floor load in N/m ²	1200
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.10
Programmes	
Short	•
Features	
Customer Service interface	•
Extensive components (option)	•
Programmes	
Medium	•
Long	•
Features	
1 door dispenser for rinsing agent	•
1 door dispenser for powder cleaning agent	•
Multi-component filter system	•
Variable-speed heater pump	•
Load carrier – direct coupling	•
In-door salt container	•
Wash cabinet seamlessly welded using laser technology	•
Heater elements outside wash cabinet	•
Wash cabinet made from high-quality stainless steel (1.4301/304)	•
Connection options	
External dispensing modules	•
Standards, test certificates and symbols	
VDE (electrical safety)	•
IP safety class according to EN 60529: IP 21	•
EN 61010-2-040	•
RoHS guideline 2011/65/EU	•
WRAS	•
Machinery Directive 2006/42/EC	•
Standards, test certificates and symbols	
EN 61010-1	•