


KWT 6834 SGS

Freestanding wine unit

FlexiFrame and SommelierSet for the perfect enjoyment of your wine.



- Simultaneous wine storage in separate temperature zones
- Odourless refrigeration section thanks to Active AirClean filters
- Present your wine in the perfect light – LED lighting
- Optimum wine protection through UV filters in tinted glass front
- Perfect enjoyment of your wine with the SommelierSet



EAN: 4002515716670 / Material number: 10409090 /  
Old Material Number: 36683400EU2

<b>Appliance category</b>	
Wine conditioning unit	•
<b>Construction type</b>	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Casing colour	Stainless Steel
Wine compartment lighting	LED illumination
<b>User convenience</b>	
Networking with Miele@home	•
Accessories required	XKM 3100 W
Active AirClean filter	•
DynaCool	•
SoftClose	•
Number of shelves	13
Number of FlexiFrame racks	10
SommelierSet	•
NoteBoard	Yes
Bottle presenter	•
<b>Control system</b>	
Operating concept	TouchControl
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
No. of temperature zones	3
Min. temperature setting range in °C	5
Max. temperature setting range in °C	20
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	G
Annual energy consumption in kWh	205.50
Energy consumption in 24 h in kWh	0.56
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
<b>Technical data</b>	
Appliance width in mm	700
Appliance height in mm	1920
Appliance depth in mm	746
Weight in kg	144.0
Climate class	SN-ST
Refrigerator compartment in l	503
Wine compartment in l	503
Total usable capacity in l	503
0.75 l Bordeaux bottle capacity (no. of bottles)	178 bottles

KWT 6834 SGS

Freestanding wine unit

FlexiFrame and SommelierSet for the perfect enjoyment of your wine.



EAN: 4002515716670 / Material number: 10409090 /


Old Material Number: 36683400EU2

Storage time in case of fault in h	0
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	35
Current consumption (mA)	1500
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.8


## KWT 6834 SGS

Freestanding wine unit


FlexiFrame and SommelierSet for the perfect enjoyment of your wine.



KWT6831SG, KWT6832SGS, KWT6833SG,  
KWT6834SGS (Installation drawings)



KWT6831SG, KWT6832SGS, KWT6833SG,  
KWT6834SGS (Installation drawings)



KWT6831SG, KWT6833SG, KWT6832SGS,  
KWT6834SGS (Installation drawings)