

DA 396-7 Classic  
Wall mounted cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



- Design – 598 mm wide trapezoidal canopy
- Powerful – 500 m<sup>3</sup>/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation



EAN: 4002515789780 / Material number: 10558520 / Old Material Number: 28396750GB

<b>Construction type</b>	
Wall mounted cooker hood	•
<b>Construction type and design</b>	
Colour	Stainless steel
<b>Operating modes</b>	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
Active charcoal filter (order separately)	DKF 12-P
<b>Design</b>	
Variable height available as customisation on request	•
<b>User convenience</b>	
Electronic controls	•
Power levels (number without Booster level)	3
Programmable Booster level switch-off	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A+++ – D)	C
Annual energy consumption in kWh/year	59.1
Fluid dynamic efficiency class	D
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
<b>Lighting</b>	
LED	•
Number x W	2 x 3 W
Light intensity in Lx	360 lx
Colour temperature in K	3000 Kelvin
<b>Fan</b>	
Dual-action fan	•
AC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	150
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	250
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	350
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	500
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	41.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	47.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	55.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	62.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	26.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	34.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	40.0

DA 396-7 Classic  
Wall mounted cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515789780 / Material number: 10558520 / Old Material Number: 28396750GB

Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13 47.0

#### Recirculation

Air throughput in Level 1 (m<sup>3</sup>/h) according to EN 61591 100

Air throughput in Level 2 (m<sup>3</sup>/h) according to EN 61591 150

Air throughput in Level 3 (m<sup>3</sup>/h) according to EN 61591 250

Air throughput in Booster level 1 (m<sup>3</sup>/h) according to EN 61591 350

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3 48.0

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3 55.0

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3 61.0

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3 68.0

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13 34.0

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13 41.0

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13 47.0

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13 53.0

#### Safety

Safety switch-off

•

#### Technical data

Overall hood height for extraction mode and external in mm 695–1015

Overall hood height for recirculation and external in mm 825–1145

Overall height for vented and external in in. (mm) 695

Canopy width in mm 598

Overall height for extraction mode and external mode cooker hoods in mm 1015

Canopy height in mm 120

Overall height for recirculation in in. (mm) 825

Canopy depth in mm 520

Overall height for recirculation mode cooker hoods in mm 1145

Minimum height above electric hobs in mm 450

Net weight in kg 21.0

Length of supply lead in m 1.5

Standard plug fitted

•

Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm 650

Total rated load in kW 0.12

Voltage in V 230

Fuse rating in A 10

Number of phases 1

Frequency in Hz 50

#### Installation notes

Extraction ducting connection at top

•

Extraction connection at top and rear

•

Diameter of exhaust duct in mm 150

Telescopic chimney

•

DA 396-7 Classic

Wall mounted cooker hood

with energy-efficient LED lighting and light-touch switches for easy use.




EAN: 4002515789780 / Material number: 10558520 / Old Material Number: 28396750GB

Optional accessories	
Active charcoal filter	Nein
Active charcoal filter, can be reactivated	DKF 12-R

## DA 396-7 Classic

Wall mounted cooker hood

with energy-efficient LED lighting and light-touch switches for easy use.



DA 396-6 (Installation drawing)

1) Extraction, 2) Recirculation, 3) Ventilation grille at top for recirculation, 4) Installation cut-out (5 not required for recirculation)