

DA 2668

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



- Customised kitchen design – fully integrated in 580 mm width
- Unique user convenience – Con@ctivity
- Powerful – 585 m<sup>3</sup>/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Efficient filtration- 10-ply stainless-steel grease filter

A<sup>+</sup>

EAN: 4002516001522 / Material number: 10851380 / Old Material Number: 28266855GB

<b>Construction type</b>	
Integrated extractor	•
<b>Operating modes</b>	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKF 19-P
<b>Design</b>	
Colour	Stainless steel
Edge extraction	•
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A+++ – D)	A+
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	28.4
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
<b>Lighting</b>	
LED	•
Number x W	2 x 4,5 W
Light intensity in Lx	700 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
<b>Fan</b>	
Dual-action fan	•
DC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	175
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	265
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	365
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	585
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	35.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	44.0

DA 2668

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516001522 / Material number: 10851380 / Old Material Number: 28266855GB

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	51.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	64.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	21.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	29.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	37.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	50.0
<b>Recirculation</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	115
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	200
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	330
Air throughput in Booster level 1 (m <sup>3</sup> /h) according to EN 61591	490
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	46.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	56.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	64.0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	74.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	42.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	49.0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	60.0
<b>Safety</b>	
Safety switch-off	•
<b>Technical data</b>	
Canopy width in mm	580
Canopy height in mm	63
Canopy depth in mm	293
Minimum height above electric hobs in mm	450
Minimum height above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Net weight in kg	12.0
Length of supply lead in m	1.5
Standard plug fitted	•
Total rated load in kW	0.08
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
<b>Installation notes</b>	
Extraction ducting connection at top	•

DA 2668

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516001522 / Material number: 10851380 / Old Material Number: 28266855GB

Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Combination with WiFi-enabled Miele hob	recommended
<b>Accessories included</b>	
Non-return flap	•
<b>Optional accessories</b>	
Active charcoal filter	Nein