

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



- Customised kitchen design – fully integrated in 880 mm width
- Unique user convenience – Con@ctivity
- Powerful – 640 m³/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Elegant and efficient – edge extraction panels




EAN: 4002515978788 / Material number: 10851390 /
Old Material Number: 28269835GB

Construction type	
Integrated extractor	•
Appliance Colour	Brilliant white
Operating modes	
Type of air guide	Can be retrofitted
Active charcoal filter (order separately)	DKF 19-P
Design	
Edge extraction	•
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Booster levels	1
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
Efficiency and sustainability	
Annual energy consumption in kWh/year	28.6
Energy efficiency class (A+++ – D)	A+
ECO motor	•
PowerManagement system	•
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Cleaning and care	
Easy-to-clean canopy interior – CleanCover	•
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	4 x 3 W
Light intensity in lx	650 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	300
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in booster level 1 (m ³ /h)	640
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36.0

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515978788 / Material number: 10851390 /
Old Material Number: 28269835GB

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3

44.0

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3

51.0

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3

62.0

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13

22.0

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13

30.0

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13

37.0

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13

48.0

Recirculation

Air throughput in Level 1 (m³/h) according to EN 61591

135

Air throughput in Level 2 (m³/h) according to EN 61591

220

Air throughput in Level 3 (m³/h) according to EN 61591

365

Air throughput in Booster level 1 (m³/h) according to EN 61591

535

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3

47.0

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3

55.0

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3

62.0

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3

74.0

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13

32.0

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13

41.0

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13

48.0

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13

59.0

Safety

Safety switch-off

•

Single-ply safety glass (ESG)

•

Technical data

Canopy width in mm

880

Canopy height in mm

63

Canopy depth in mm

293

Net weight in kg

14.0

Length of supply lead in m

1.5

Standard plug fitted

•

Minimum height above electric hobs in mm

450

Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm

650

Voltage in V

230

Fuse rating in A

10

Number of phases

1

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515978788 / Material number: 10851390 /
Old Material Number: 28269835GB

Total rated load in kW	0.09
Frequency in Hz	50

Installation notes

Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Combination with WiFi-enabled Miele hob	recommended

Accessories included

Non-return flap	•
-----------------	---