

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



- Customised kitchen design – fully integrated in 880 mm width
- Unique user convenience – Con@ctivity
- Powerful – 640 m³/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Elegant and efficient – edge extraction panels



EAN: 4002516001492 / Material number: 10851400 / Old Material Number: 28269855GB

| | |
|---------------------------------------------------------------------------|--------------------|
| Construction type | |
| Integrated extractor | • |
| Construction type and design | |
| Colour | Stainless steel |
| Operating modes | |
| Type of air guide | Can be retrofitted |
| Recirculation conversion kit (order separately) | DUU 151 |
| Active charcoal filter (order separately) | DKF 19-P |
| Design | |
| Edge extraction | • |
| User convenience | |
| Miele@home | • |
| Automatic function Con@ctivity | • |
| Electronic controls | • |
| Power levels (number without Booster level) | 3 |
| Miele@mobile app | • |
| Run-on time 5/15 min. | • |
| Programmable Booster level switch-off | • |
| Grease filter saturation indicator | • |
| Grease filter saturation indicator programmable | • |
| Active charcoal filter saturation indicator programmable | • |
| Easy-to-clean canopy interior – CleanCover | • |
| Efficiency and sustainability | |
| Energy efficiency class (A+++ – D) | A+ |
| ECO motor | • |
| PowerManagement system | • |
| Annual energy consumption in kWh/year | 28.6 |
| Fluid dynamic efficiency class | A |
| Lighting efficiency class | A |
| Grease filtering efficiency class | A |
| Filter system | |
| Number of dishwasher-safe stainless steel grease filters (10-ply) | 2 |
| Lighting | |
| LED | • |
| Number x W | 4 x 3 W |
| Light intensity in Lx | 650 lx |
| Colour temperature in K | 3500 Kelvin |
| Dimmer function | • |
| Fan | |
| Dual-action fan | • |
| DC motor | • |
| Exhaust air | |
| Air throughput in Level 1 (m ³ /h) according to EN 61591 | 200 |
| Air throughput in Level 2 (m ³ /h) according to EN 61591 | 300 |
| Air throughput in Level 3 (m ³ /h) according to EN 61591 | 400 |
| Air throughput in Booster level (m ³ /h) according to EN 61591 | 640 |
| Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3 | 36.0 |

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516001492 / Material number: 10851400 / Old Material Number: 28269855GB

| | |
|------------------------------------------------------------------------------------------|------|
| Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3 | 44.0 |
| Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3 | 51.0 |
| Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3 | 62.0 |
| Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13 | 22.0 |
| Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13 | 30.0 |
| Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13 | 37.0 |
| Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13 | 48.0 |
| Recirculation | |
| Air throughput in Level 1 (m ³ /h) according to EN 61591 | 135 |
| Air throughput in Level 2 (m ³ /h) according to EN 61591 | 220 |
| Air throughput in Intensive level (m ³ /h) according to EN 61591 | 535 |
| Air throughput in Level 3 (m ³ /h) according to EN 61591 | 365 |
| Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3 | 47.0 |
| Noise power level in Intensive level (dB(A) re 1 pW) according to EN 60704-3 | 74.0 |
| Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3 | 55.0 |
| Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3 | 62.0 |
| Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13 | 32.0 |
| Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13 | 41.0 |
| Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13 | 48.0 |
| Noise pressure level in Intensive level (dB(A) re 20 µPa) according to EN 60704-2-13 | 59.0 |
| Safety | |
| Safety switch-off | • |
| Technical data | |
| Canopy width in mm | 880 |
| Canopy height in mm | 63 |
| Canopy depth in mm | 293 |
| Minimum height above electric hobs in mm | 450 |
| Net weight in kg | 14.0 |
| Length of supply lead in m | 1.5 |
| Standard plug fitted | • |
| Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm | 650 |
| Total rated load in kW | 0.09 |
| Voltage in V | 230 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Frequency in Hz | 50 |

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516001492 / Material number: 10851400 / Old Material Number: 28269855GB

| Installation notes | |
|-----------------------------------------|-------------|
| Extraction ducting connection at top | • |
| Extraction connection at top and rear | • |
| Diameter of exhaust duct in mm | 150 |
| Combination with WiFi-enabled Miele hob | recommended |
| Accessories included | |
| Non-return flap | • |
| Optional accessories | |
| Active charcoal filter | Nein |