

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



- 7-segment display with retractable rotary controls – EasyControl
- Minimal cleaning effort – Pyrolytic cleaning
- Lots of room and flexibility – 76 l oven capacity on 5 levels
- Easy handling – FlexiClip runners
- Protects against burns – touch-cool fronts



EAN: 4002516156710 / Material number: 11093000 /
Old Material Number: 22226795GB

General information	
Model identifier	H 2267-1 BP Active
Manufacturer material number	11093000
EAN number	4002516156710
Marketing class	Silver
Construction type and design	
Built-in oven	•
Colour	Stainless steel/Clean Steel
Retractable rotary controls	•
Convenience features	
Rapid heat-up	•
Operating modes	
Fan plus	•
Conventional heat	•
Intensive bake	•
Fan grill	•
Grill	•
Bottom heat	•
User convenience	
Display	EasyControl
Time of day display	•
Minute minder	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
Individual settings	•
Efficiency	
Energy efficiency class (A+++ – D)	A+
Cleaning and care	
Stainless steel/CleanSteel finish	•
Pyrolytic self-cleaning	•
Hinged grill element	•
CleanGlass door	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Technical data	
Oven compartment volume in l	76
No. of shelf levels	5
Numbered shelf levels	•
Oven light	1 halogen spot
Niche width min. in mm	560
Niche width max. in mm	568

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



EAN: 4002516156710 / Material number: 11093000 /
Old Material Number: 22226795GB

Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Weight in kg	47.0
Total rated load in kW	3.60
Voltage in V	220 - 240
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Length of mains connection cable in m	1.50
Replacing lamps	Customer


Accessories included

Baking tray with PerfectClean	1
Universal tray with PerfectClean HUBB 71	1
Baking and roasting rack without PerfectClean	1
FlexiClip runners HFC 70-C (pair)	1
Removable side runners (pair)	1
Grilling and roasting insert with PerfectClean	1

H 2267-1 BP Active


Oven

with a timer, pyrolytic cleaning & FlexiClip runners.




installation H7000 XL, installation drawing

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm²




installation H7000 XL, installation drawing, GB, AU

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm²




side view H7000 XL, installation drawings, GB, AU

22 mm – glass, 23.3 mm – metal




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings

If the oven is to be installed under a hob, follow the instructions for installing the hob and the height of the hob.




H226x-1B/BP/E/EP/I/IP, H24xx installation drawings

1) 400 mm, 2) 360 mm, 3) 42 mm, 4) 27 mm, 5) 32.5 mm




Installation H7000 BM XL, installation drawings



side view H7000 XL build-under, installation drawing, GB, AU

22 mm – glass, 23.3 mm – metal




Side view Kombi BM XL, installation drawings

22 mm – glass, 23.3 mm – metal

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



Installation Kombi BM XL, installation drawings

22 mm – glass, 23,3 mm – metal