

PTD 703 [WES]

Tank dishwasher

with short cycles for fast turnaround times - incl. integrated softener.



- Max. cleaning performance*: 1170 plates/h
- Simple and flexible operation – full-touch display
- Economical and efficient – 2.00 l water consumption of only** per cycle
- Always the right programme – item-specific solutions
- Perfect integration – suitable for installation in run of units

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

** The specified value refers to the ECO programme. Water consumption depends on the selected programme.

EAN: 4002516104315 / Material number: 11097710 / Old Material Number: 61070304D

Construction type and version

Construction type	Freestanding dishwasher, can be built under
Range	Professional
Model	Universal
Wash system	Tank front loader
Number of levels	1
Front	Stainless steel
Lid	Stainless Steel
Side panels	Stainless steel
Rear panel	Plastic
Tank volume in l	15.3

Application

Suitable for retirement and care homes	•
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for guesthouses	•
Suitable for canteens	•
Suitable for child care facilities	•
Suitable for universities and schools	•
Suitable for small businesses	•
Suitable for fast food restaurants	•
Suitable for sports clubs	•

Performance data

Tested virucidal efficacy	•
Circulation pump Qmax in l/min.	200
Shortest programme duration in sec.	55
Maximum final rinse temperature in °C	90
Cleaning performance, plates/h	1170
Cleaning performance, baskets/h	66
Service life in wash cycles	250000

Control system

Control system	Electronic controls
Programme selection	Full-touch display
Automatic On/Off standby switch	•
Dishwashing programmes [number]	3
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable rinse time	•
Coloured programme sequence indicator	•
Choice of display language	•

Standard electrical connection

Electrical connection	3N AC 380-415V 50HZ
Tank heater rating in kW	1.80
Boiler heater rating in kW	4.90
Total connected load in kW	7.90
Fuse rating in A	16

PTD 703 [WES]

Tank dishwasher

with short cycles for fast turnaround times - incl. integrated softener.



EAN: 4002516104315 / Material number: 11097710 / Old Material Number: 61070304D

Possible voltage variant 1

Electrical connection	3 AC 230V 50HZ
Heater rating in kW	0.00
Total connected load in kW	5.00
Fuse rating in A	20

Possible voltage variant 2

Electrical connection	3N AC 380-415V 50HZ
Heater rating in kW	0.00
Total connected load in kW	6.00
Fuse rating in A	10

Possible voltage variant 3

Electrical connection	3 AC 230V 50HZ
Heater rating in kW	0.00
Total connected load in kW	7.30
Fuse rating in A	25

Possible voltage variant 4

Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	2.60
Fuse rating in A	13

Possible voltage variant 5

Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	3.20
Fuse rating in A	16

Possible voltage variant 6

Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	4.20
Fuse rating in A	20

Water connection/drainage

Cold or hot water [number]	1
Maximum temperature of inlet water in °C	60
Required flow pressure in bar	1.00-6.00
Drain pump head height from floor level, max. in c	60
Booster pump	•
Integrated water softener	•
Maximum water hardness in mmol/l	5.35
Water consumption per wash cycle in l	2.00
Length of water inlet hose in cm	150
Length of water drain hose in cm	150

Dimensions and weight

External dimensions, height in mm	820
Maximum height adjustment in mm	35.00
External dimensions, net width in mm	600
External dimensions, net depth in mm	617
External dimensions, gross height in mm	870
External dimensions, gross width in mm	650
External dimensions, gross depth in mm	667

PTD 703 [WES]

Tank dishwasher

with short cycles for fast turnaround times - incl. integrated softener.



EAN: 4002516104315 / Material number: 11097710 / Old Material Number: 61070304D

Usable space in wash cabinet, height in mm	404
Usable space in wash cabinet, width in mm	510
Usable space in wash cabinet, depth in mm	568
In-feed height above floor in mm	328
Net weight [kg]	69
Gross weight in kg	79
Maximum floor load in N/m ²	790
Emissions data	
Emissions – sound pressure at workplace	55 dB(A) re 20 µPa
Programmes	
Programme for light soiling	•
Programme for normal soiling	•
Programme for heavy soiling	•
Additional programme options	•
Wash ware specific	•
Self-cleaning	•
Descaling	•
Basket design	
Without baskets	•
Features	
Integrated dispensing pump/dispensing module for rinsing agent	•
Integrated dispensing pump/dispensing module for liquid cleaning agent	•
Stainless steel rear panel of splash protection class IPX5 (optional)	•
Highly effective filter system	•
Spray arm monitor for all spray arms	•
Wash cabinet made from high-quality stainless steel	•
Temperature indicator for tank and boiler	•
Hygienic tank wash cabinet	•
Rotating spray system (top + bottom)	•
A wide range of accessories (optional)	•
Connection options	
Suction lances for external media canisters [number]	2
Standards, test certificates and symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
Splash-proof IPX3	•
DIN EN 17735	•
UKCA	•