

PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 88 min.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry
- Future-proof networking via WiFi

EAN: 4002516126027 / Material number: 11105560 / Old Material Number: 52908453GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	2.60
Specific energy consumption in kWh/kg	0.49
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.49
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.41
Programme duration in min.	88
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	88
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	75
Control system	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•

PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 88 min.



EAN: 4002516126027 / Material number: 11105560 / Old Material Number: 52908453GB

Language can be selected easily at any time

Standard electrical connection	
Heating type	Electric
Electrical connection	220-230V~ 50/60HZ
Electric heater rating in kW	2.52-2.76
Total connected load in kW	2.76-2.99
Fuse rating in A	13
Possible voltage variant 1	
Heater rating in kW	2.76
Fuse rating in A	13-13
Possible voltage variant 2	
Heater rating in kW	6.14
Total connected load in kW	6.40
Fuse rating in A	16-16
Dimensions and weight of dryer	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	51.5
Gross weight in kg	57
Maximum floor load in N/m ²	920
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•

PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 88 min.



EAN: 4002516126027 / Material number: 11105560 / Old Material Number: 52908453GB

Complies with Machinery Directive 2006/42/EC

