

## PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Performance 8.0 kg in 52 min.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use unparalleled Miele quality
- Max. user convenience, full-touch colour display M Touch Flex
- Precision drying of all fabrics PerfectDry
- Future-proof networking via WiFi

EAN: 4002516134114 / Material number: 11105580 / Old Material Number: 52908354GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Lotus white
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in I	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in I/hour	4.80
Specific energy consumption in kWh/kg	0.50
Specific energy consumption for Cottons/Normal drying	0.50
programme with residual moisture at 48 % in kW	0.00
Specific energy consumption for mixed fibre fabrics/Normal	0.42
drying programme with residual moisture a	
Programme duration in min.	52
Programme duration for Cottons/Normal drying programme	52
with residual moisture at 48 % in minutes	
Programme duration for mixed fibre fabrics/Normal drying	57
programme with residual moisture at 40 % in	
Control system	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture
	controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•



## PDR 908 [EL] Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Performance 8.0 kg in 52 min.



Language can be selected easily at any time Standard electrical connection Heating type Electric 220-230V~ 50/60HZ Electrical connection Electric heater rating in kW 4.78-5.22 Total connected load in kW 5.03-5.47 Fuse rating in A 25 Dimensions and weight of dryer External dimensions, height in mm 850 External dimensions, width in mm 596 External dimensions, depth in mm 717 External dimensions, gross height in mm 940 External dimensions, gross width in mm 660 820 External dimensions, gross depth in mm Net weight in kg 51.5 Gross weight in kg 57 Maximum floor load in N/m<sup>2</sup> 920 **Emissions data** <70 dB(A) re 20 µPa Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h 0.76 Features Intelligent drum reversal • Axial airflow • Large-surface filter • PerfectDry • SoftLift drum ribs • Low temperature function • Communication slot • Drying basket (optional) • Drum lighting • • Machine-independent accessories **Connection options** Payment system (optional) ٠ Optical interface for service access • Peak load cut-out/energy management (optional) • LAN/WiFi module (optional) • WiFiConn@ct . Standards, test certificates and symbols CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 • WEEE • UKCA • Complies with Machinery Directive 2006/42/EC •

EAN: 4002516134114 / Material number: 11105580 / Old Material Number: 52908354GB