

## PWM 507 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 59 min.



- Drum volume 64 l, load size 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- 22 % less water consumption and 28 % less energy consumption\*
- Future-proof networking via WiFi

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.



EAN: 4002516363767 / Material number: 11105770 / Old Material Number: 51507353GB

### Construction type and version

Construction type	Front-loader, stackable
Range	Performance
Front	Stainless steel
Control panel colour	Stainless steel
Load in kg	7.0
Drum volume in l	64
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel made of stainless steel	•

### Application

Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•

### Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	7.00
Specific energy consumption for cold water connection in kWh/kg	0.14
Specific water consumption for hot water connection in l/kg	6.60
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	49.0
Energy consumption with cold water connection in kW	0.98
Programme duration in minutes with cold water connection	69
Water consumption with hot water connection in l	46.0
Energy consumption with hot water connection in kW	0.44
Programme duration in minutes with cold water and hot water connection	59
Residual moisture with cold rinse in %	48

## PWM 507 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 59 min.



EAN: 4002516363767 / Material number: 11105770 / Old Material Number: 51507353GB

Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
<b>Control system</b>	
Control system	M Select
Programmability	programmable
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	230V~
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	13
<b>Possible voltage variant 1</b>	
Electrical connection	2N~ 400V 50HZ
Heater rating in kW	5.30
Total connected load in kW	5.50
Fuse rating in A	13
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	714
External dimensions, gross height in mm	944
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	100.0
Gross weight in kg	104
Maximum floor load in N	2820
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00

## PWM 507 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 59 min.



EAN: 4002516363767 / Material number: 11105770 / Old Material Number: 51507353GB

### Features

3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
Pre-ironing	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•

### Efficiency and sustainability

Load size for the "Eco 40–60" programme in kg	7.0
Energy efficiency class (A–G)	A
Spin efficiency class (A–G)	A
Weighted energy consumption per 100 cycles in the "Eco 40–60" programme in kWh	45
Weighted water consumption per cycle in the "Eco 40–60" programme in l	37
Airborne noise emission rating (spin cycle) (A–D)	A
Airborne noise emission during spin cycle in dB(A) re 1 pW	72
Airborne noise emission during spin cycle in dB(A) re 1 pW	199
Recycling rate in %	95

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•

### Standards, test certificates and symbols

CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WRAS	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•