

## PWM 907 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 49 min.



- Drum volume 64 l, load size 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience w. full-touch colour display –M Touch Flex
- 22 % less water consumption and 28 % less energy consumption\*
- Future-proof networking via WiFi

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516364214 / Material number: 11106470 / Old Material Number: 51907151GB

### Construction type and design

|  |                         |
|--|-------------------------|
| Construction type                              | Front-loader, stackable |
| Range  | Performance Plus        |
| Front  | Lotus white             |
| Control panel colour                           | Stainless steel         |
| Load in kg                                     | 7.0                     |
| Drum volume in l                               | 64                      |
| Door opening [Ø] in mm                         | 300                     |
| Door opening angle in degrees                  | 167                     |
| Door hinge                                     | right                   |
| Maintenance-free synchronous motor             | •                       |
| Honeycomb drum with perforated drum rear panel | •                       |

### Application

|   |   |
|---|---|
| Suitable for the hotel and catering industry          | • |
| Suitable for launderettes                             | • |
| Suitable for residential homes and apartments         | • |
| Suitable for dry cleaners                             | • |
| Suitable for commercial laundries                     | • |
| Suitable for small businesses                         | • |
| Suitable for universities, nurseries, and schools     | • |
| Suitable for hospitals                                | • |
| Suitable for camp sites                               | • |
| Suitable for sports clubs                             | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for doctors' and dentists' practices         | • |
| Suitable for the petrochemicals industry              | • |
| Suitable for the food-processing industry             | • |
| Suitable for amusement parks & holiday complexes      | • |
| Suitable for state/community care facilities          | • |

### Performance data

|  |       |
|--|-------|
| Tested virucidal efficacy  | •     |
| Proven hygiene   | •     |
| Specific water consumption for cold water connection in l/kg           | 7.00  |
| Specific energy consumption for cold water connection in kWh/kg        | 0.14  |
| Specific water consumption for hot water connection in l/kg            | 6.60  |
| Specific energy consumption for hot water connection in kWh/kg         | 0.06  |
| Water consumption with cold water connection in l                      | 49.0  |
| Energy consumption with cold water connection in kW                    | 0.98  |
| Programme duration in minutes with cold water connection               | 59    |
| Water consumption with hot water connection in l                       | 46.0  |
| Energy consumption with hot water connection in kW                     | 0.44  |
| Programme duration in minutes with cold water and hot water connection | 49    |
| Residual moisture with cold rinse in %                                 | 48    |
| Residual moisture with hot rinse in %                                  | 45    |
| Spin speed in rpm  | 1600  |
| g factor   | 704   |
| Tested operating hours   | 30000 |

## PWM 907 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 49 min.



EAN: 4002516364214 / Material number: 11106470 / Old Material Number: 51907151GB

| Controls  |                                |
|---|--------------------------------|
| Control system  | M Touch Flex                   |
| Programmability   | programmable                   |
| Max. delay start in h   | 96                             |
| Time left display   | •                              |
| Programme sequence indicator                                      | •                              |
| Language can be selected easily at any time                       | •                              |
| Dispensing  |                                |
| Detergent drawer  | 3 compartments                 |
| CapDosing   | •                              |
| Flexible dispensing adapter (optional)                            | •                              |
| Maximum number of connections for liquid dispenser pumps [number] | 6                              |
| Empty sensor  | •                              |
| Standard electrical connection                                    |                                |
| Heating type  | Electric                       |
| Electrical connection   | 2N~ 400V 50HZ                  |
| Heater rating in kW   | 5.30                           |
| Total connected load in kW  | 5.50                           |
| Fuse rating in A  | 13                             |
| Possible voltage variant 1  |                                |
| Electrical connection   | 230V~                          |
| Heater rating in kW   | 2.65                           |
| Total connected load in kW  | 2.85                           |
| Fuse rating in A  | 13                             |
| Water connection/drainage   |                                |
| Cold water [number]   | 1x 1/2" hose w/ 3/4" th. union |
| Hot water [number]  | 1x 1/2" hose w/ 3/4" th. union |
| Drain pump  | DN 22                          |
| Dimensions and weight   |                                |
| External dimensions, height in mm                                 | 850                            |
| External dimensions, width in mm                                  | 596                            |
| External dimensions, depth in mm                                  | 714                            |
| External dimensions, gross height in mm                           | 940                            |
| External dimensions, gross width in mm                            | 660                            |
| External dimensions, gross depth in mm                            | 768                            |
| Net weight in kg  | 101.0                          |
| Gross weight in kg  | 105                            |
| Maximum floor loading in N  | 2820                           |
| Emissions data  |                                |
| Emission sound pressure level in the workplace                    | <70 dB(A) re 20 µPa            |
| Heat dissipation into the room in MJ/h                            | 1.00                           |
| Features  |                                |
| 3-dimensional imbalance monitoring                                | •                              |
| Commercial shock absorbers  | •                              |
| Hard-wearing stainless-steel flange                               | •                              |
| Disinfection rinse  | •                              |
| EcoSpeed  | •                              |
| Pre-ironing   | •                              |

## PWM 907 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 7.0 kg in 49 min.



EAN: 4002516364214 / Material number: 11106470 / Old Material Number: 51907151GB

|  |    |
|--|----|
| Efficient drum rib technology                  | •  |
| Temperature monitoring                         | •  |
| Special heater element                         | •  |
| Automatic load control                         | •  |
| Flow meter                                     | •  |
| LED drum lighting, class 1                     | •  |
| Communication slot                             | •  |
| Add laundry                                    | •  |
| Machine-independent accessories                | •  |
| <b>Efficiency and sustainability</b>           |    |
| Recycling rate in %                            | 95 |
| <b>Connection options</b>                      |    |
| Payment system (optional)                      | •  |
| Optical interface for service access           | •  |
| Peak load cut-out/energy management (optional) | •  |
| LAN/WiFi module (optional)                     | •  |
| WiFiConn@ct                                    | •  |
| <b>Standards, certs, symbols</b>               |    |
| CE   | •  |
| VDE-EMC  | •  |
| VDE  | •  |
| Splash-proof safety rating IPX4                | •  |
| WRAS   | •  |
| UKCA   | •  |
| WEEE   | •  |
| Complies with Machinery Directive 2006/42/EC   | •  |