

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



- Innovative cooking every day in your own home thanks to M Chef
- Improved results in terms of texture and uniformity
- Demanding dishes made easy with Gourmet Assistant and Gourmet Pro
- Multi-stage cooking with M Chef Menu
- Time savings of up to 70 % combined with excellent quality

EAN: 4002516159957 / Material number: 11108000 / Old Material Number: 20786025GB

Construction type and design	
Dialog cooker	•
Appliance Colour	Obsidian black
Back-lit M Chef logo	•
Convenience features	
M Chef innovative cooking	•
Private Dining	•
Gourmet Profi	•
Gourmet Assistant	•
Pre-heating	•
Food probe	•
Keeping warm	•
Crisp function	•
Operating modes	
M Chef + Fan plus	•
M Chef + Conventional heat	•
M Chef + Intensive bake	•
M Chef + Moisture plus	•
M Chef + Auto roast	•
M Chef + Full grill	•
M Chef + Fan grill	•
Extremely gentle defrosting	•
M Chef menu	•
Auto roast	•
Grill operating modes	•
Grill	•
Economy grill	•
Fan plus	•
Intensive bake	•
Moisture plus	•
Moisture plus with Fan plus	•
Moisture plus with Conventional heat	•
Moisture plus with Intensive bake	•
Moisture plus with Conventional heat	•
Low temperature cooking	•
Conventional heat	•
Top heat	•
Bottom heat	•
Fan grill	•
Special applications	•
User convenience	
Networking with Miele@home	•
Display	M Touch
SoftOpen	•
MultiLingua	•
MyMiele	•
Help function	•
Individual settings	•
Programmable timed steam injection	•
Polyphonic buzzers	•

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516159957 / Material number: 11108000 / Old Material Number: 20786025GB

Time of day display	•
Clock synchronisation	•
Date display	•
Minute minder	•
Programmable start of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Suggested Gourmet units	•
Recommended temperature	•
Sabbath programme	•
Efficiency and sustainability	
Residual heat utilisation	•
Cleaning convenience	
Pyrolytic self-cleaning	•
Heated catalyser	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Sensor lock	•
Technical data	
Oven compartment volume in l	50
No. of shelf levels	4
Oven light	BrilliantLight
Electronic temperature regulation min. in °C	30
Electronic temperature regulation max. in °C	300
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Appliance width in mm	595
Appliance height in mm	596
Temperatures in °C	30–300
Appliance depth in mm	568
Weight in kg	60.8
Total rated load in kW	3.70
Voltage in V	220-240
Frequency in Hz	50
Number of phases	1
Fuse rating in A	16
Mains cable	•
Length of supply lead in m	2.00
Replacing lamps	Customer Service
Accessories supplied	
Baking tray with PerfectClean	1
Universal tray with PerfectClean	1
Baking and roasting rack PyroFit	1

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516159957 / Material number: 11108000 / Old Material Number: 20786025GB

Descaling tablets

2

Available display languages


Available display languages through MultiLingua

bahasa malaysia, dansk,
deutsch, english, español,
français, hrvatski, italiano,
magyar, nederlands,
norsk, polski, português,
русский, română,
slovenčina, slovenščina,
srpski, suomi, svenska,
türkçe, українська, čeština,
ελληνικά, , , ,


DO 7860

Dialog oven


- from designer-level kitchen to star rated kitchen.




DO7860, installation drawings
22 mm – glass, 23,3 mm – metal




DO7860, DO7860 C (CN), installation drawings, GB, AUS, CN
22 mm – glass, 23.3 mm – metal




DO7860, DO7860C (CN), installation drawings




DO7860, DO7860C (CN), installation drawings



DO7860, installation drawings
1) Mains Connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm²



DO7860, DO7860 C (CN), installation drawings, GB, AUS, CN
1) Mains connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm²



DG7x40, DGC7x4x, DGC7x6x, DG7635, DGM7x4x, DO7, H2860B/BP, H7240BM, H7x40BM, H7x4xB/BP, H7x6xB/BP, installation drawings

1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 27 mm, 5) 32.5 mm