

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



- Innovative cooking every day in your own home thanks to M Chef
- Improved results in terms of texture and uniformity
- Demanding dishes made easy with Gourmet Assistant and Gourmet Pro
- Multi-stage cooking with M Chef Menu
- Time savings of up to 70 % combined with excellent quality

EAN: 4002516160137 / Material number: 11108020 / Old Material Number: 20786045GB

<b>Construction type and design</b>	
Dialog cooker	•
PureLine	•
Appliance Colour	Stainless steel/Clean Steel
Back-lit M Chef logo	•
<b>Convenience features</b>	
M Chef innovative cooking	•
Private Dining	•
Gourmet Profi	•
Gourmet Assistant	•
Pre-heating	•
Food probe	•
Keeping warm	•
Crisp function	•
<b>Operating modes</b>	
M Chef + Fan plus	•
M Chef + Conventional heat	•
M Chef + Intensive bake	•
M Chef + Moisture plus	•
M Chef + Auto roast	•
M Chef + Full grill	•
M Chef + Fan grill	•
Extremely gentle defrosting	•
M Chef menu	•
Auto roast	•
Grill operating modes	•
Grill	•
Economy grill	•
Fan plus	•
Intensive bake	•
Moisture plus	•
Moisture plus with Fan plus	•
Moisture plus with Conventional heat	•
Moisture plus with Intensive bake	•
Moisture plus with Conventional heat	•
Low temperature cooking	•
Conventional heat	•
Top heat	•
Bottom heat	•
Fan grill	•
Special applications	•
<b>User convenience</b>	
Networking with Miele@home	•
Display	M Touch
SoftOpen	•
MultiLingua	•
MyMiele	•
Help function	•
Individual settings	•
Programmable timed steam injection	•

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516160137 / Material number: 11108020 / Old Material Number: 20786045GB

Polyphonic buzzers	•
Time of day display	•
Clock synchronisation	•
Date display	•
Minute minder	•
Programmable start of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Suggested Gourmet units	•
Recommended temperature	•
Sabbath programme	•
<b>Efficiency and sustainability</b>	
Residual heat utilisation	•
<b>Cleaning convenience</b>	
Stainless steel/CleanSteel finish	•
Pyrolytic self-cleaning	•
Heated catalyser	•
<b>Safety</b>	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Sensor lock	•
<b>Technical data</b>	
Oven compartment volume in l	50
No. of shelf levels	4
Oven light	BrilliantLight
Electronic temperature regulation min. in °C	30
Electronic temperature regulation max. in °C	300
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Appliance width in mm	595
Appliance height in mm	596
Temperatures in °C	30–300
Appliance depth in mm	569
Weight in kg	60.8
Total rated load in kW	3.70
Voltage in V	220-240
Frequency in Hz	50
Number of phases	1
Fuse rating in A	16
Mains cable	•
Length of supply lead in m	2.00
Replacing lamps	Customer Service
<b>Accessories supplied</b>	
Baking tray with PerfectClean	1

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516160137 / Material number: 11108020 / Old Material Number: 20786045GB

Universal tray with PerfectClean	1
Baking and roasting rack PyroFit	1
Descaling tablets	2

**Available display languages**


Available display languages through MultiLingua

bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands,  
norsk, polski, português,  
русский, română,  
slovenčina, slovenščina,  
srpski, suomi, svenska,  
türkçe, українська, čeština,  
ελληνικά, , , ,


## DO 7860

### Dialog oven


- from designer-level kitchen to star rated kitchen.




DO7860, installation drawings  
22 mm – glass, 23,3 mm – metal




DO7860, DO7860 C (CN), installation drawings, GB, AUS, CN  
22 mm – glass, 23.3 mm – metal




DO7860, DO7860C (CN), installation drawings




DO7860, DO7860C (CN), installation drawings



DO7860, installation drawings  
1) Mains Connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>



DO7860, DO7860 C (CN), installation drawings, GB, AUS, CN  
1) Mains connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>



DG2840, DG7x40, DGC7x4x, DG7x6x, DGC7x6x, DGD7635, DGM7x4x, DO7, H28B/BP, H7x4xB/BM/BP, H7x6xB/BP, installation drawing  
1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 24 mm, 5) 32.5 mm