

PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

with very low energy consumption and short programme running times. Load size 8.0 kg.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry
- Future-proof networking via WiFi

EAN: 4002516126638 / Material number: 11108030 / Old Material Number: 52908253GB

| Construction type and version | |
|--|------------------------------|
| Construction type | Front-loader, stackable |
| Range | Performance Plus |
| Front | Stainless steel |
| Fascia color | Stainless steel |
| Load in kg | 8.0 |
| Drum volume in l | 130.00 |
| Drying system | Heat pump |
| Door opening [Ø] in mm | 370 |
| Door opening angle in degrees | 167 |
| Door hinge | left |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for launderettes | • |
| Suitable for residential homes and apartments | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundries | • |
| Suitable for small businesses | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for camp sites | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for doctors' and dentists' practices | • |
| Suitable for the petrochemicals industry | • |
| Suitable for the food-processing industry | • |
| Suitable for amusement parks & holiday complexes | • |
| Suitable for state/community care facilities | • |
| Performance data | |
| Maximum evaporation capacity in l/hour | 2.80 |
| Specific energy consumption in kWh/kg | 0.20 |
| Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW | 0.20 |
| Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a | 0.17 |
| Programme duration in min. | 79 |
| Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes | 79 |
| Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in | 67 |
| Control system | |
| Control system | M Touch Flex |
| Programmability | programmable |
| User interface | Residual moisture controlled |
| Max. delay start in h | 24 |
| Time left display | • |
| Programme sequence indicator | • |

PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

with very low energy consumption and short programme running times. Load size 8.0 kg.



EAN: 4002516126638 / Material number: 11108030 / Old Material Number: 52908253GB

Language can be selected easily at any time

Standard electrical connection

| | |
|------------------------------|----------------|
| Heating type | Heat pump |
| Electrical connection | 220-240V~ 50HZ |
| Electric heater rating in kW | 0.00-0.00 |
| Total connected load in kW | 1.44 |
| Fuse rating in A | 13 |

Dimensions and weight of dryer

| | |
|---|------|
| External dimensions, height in mm | 850 |
| External dimensions, width in mm | 605 |
| External dimensions, depth in mm | 777 |
| External dimensions, gross height in mm | 940 |
| External dimensions, gross width in mm | 660 |
| External dimensions, gross depth in mm | 820 |
| Net weight in kg | 72.0 |
| Gross weight in kg | 78 |
| Maximum floor load in N/m ² | 920 |

Emissions data

| | |
|--|---------------------|
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 3.60 |

Features

| | |
|--|---|
| Intelligent drum reversal | • |
| Axial airflow | • |
| Fluff filter in the door | • |
| Low-maintenance heat exchanger filter system | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| Gentle tumble function | • |
| Condensed water drainage | • |
| Communication slot | • |
| Drying basket (optional) | • |
| Drum lighting | • |
| Machine-independent accessories | • |

Efficiency and sustainability

| | |
|--|--------|
| Contains fluorinated greenhouse gases | • |
| Hermetically sealed system | • |
| Coolant | R134a |
| Refrigerant quantity in kg | 0.61 |
| Refrigerant global warming potential in kg CO ₂ e | 1430 |
| Appliance global warming potential in kg CO ₂ e | 872.00 |

Connection options

| | |
|--------------------------------------|---|
| Payment system (optional) | • |
| Optical interface for service access | • |
| LAN/WiFi module (optional) | • |

Standards, test certificates and symbols

| | |
|---------------------------------|---|
| CE | • |
| VDE | • |
| VDE-EMC | • |
| Splash-proof safety rating IPX4 | • |
| WEEE | • |
| UKCA | • |

PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

with very low energy consumption and short programme running times. Load size 8.0 kg.



EAN: 4002516126638 / Material number: 11108030 / Old Material Number: 52908253GB

Complies with Machinery Directive 2006/42/EC

