

## M 7244 TC

Built-in microwave oven

in a design that is the perfect complement with controls on the top.



- Clear-text display with sensor controls – DirectSensor S
- Optimum and even browning – integrated Quartz grill
- Perfect defrosting and cooking – Automatic programmes
- Plenty of room – 46 l oven compartment volume and 40 cm turntable
- Popcorn at the touch of a button – Popcorn button

EAN: 4002516128311 / Material number: 11143780 / Old Material Number: 24724440GB

| General information                            |                             |
|------------------------------------------------|-----------------------------|
| Model identifier                               | M 7244 TC                   |
| Manufacturer material number                   | 11143780                    |
| EAN number                                     | 4002516128311               |
| Marketing class                                | Gold                        |
| Construction type and design                   |                             |
| Colour                                         | Stainless steel/Clean Steel |
| PureLine                                       | •                           |
| TopControl                                     | •                           |
| Appliance type and design                      |                             |
| Microwave                                      | •                           |
| Convenience features                           |                             |
| Keeping warm                                   | •                           |
| Quartz grill                                   | •                           |
| Operating modes                                |                             |
| Microwave                                      | •                           |
| Grill                                          | •                           |
| Microwave/grill combination mode               | •                           |
| Automatic programmes                           | •                           |
| User convenience                               |                             |
| Display                                        | DirectSensor S              |
| SoftOpen                                       | •                           |
| SoftClose                                      | •                           |
| MultiLingua                                    | •                           |
| Popcorn function                               | •                           |
| Time of day display                            | •                           |
| Minute minder                                  | •                           |
| Programmable end of cooking duration           | •                           |
| Programmable cooking duration                  | •                           |
| Quick microwave                                | •                           |
| Individual settings                            | •                           |
| Efficiency                                     |                             |
| Night dimming                                  | •                           |
| Power rating in off mode in W                  | 0.3                         |
| Power rating in standby mode in W              | 0.8                         |
| Time until automatic switch to off mode in min | 20                          |
| Time until automatic switch to standby in min  | 20                          |
| Cleaning and care                              |                             |
| Stainless steel/CleanSteel finish              | •                           |
| Stainless steel oven compartment               | •                           |
| CleanGlass door                                | •                           |
| Safety                                         |                             |
| Appliance cooling system and touch-cool front  | •                           |
| System lock                                    | •                           |
| Safety switch-off                              | •                           |
| Safety lock "Door" warning                     | •                           |
| Technical data                                 |                             |
| Oven compartment volume in l                   | 46                          |

## M 7244 TC

Built-in microwave oven

in a design that is the perfect complement with controls on the top.



EAN: 4002516128311 / Material number: 11143780 / Old Material Number: 24724440GB

|                                           |                 |
|-------------------------------------------|-----------------|
| Appliance dimensions (W x H x D) in mm    | 595 x 456 x 560 |
| Oven light                                | 1 LED spot      |
| Door hinging                              | Bottom          |
| Oven interior height in cm                | 23.2            |
| Turntable diameter in cm                  | 40.6            |
| Electronically controlled microwave power | •               |
| Microwave power levels in W               |                 |
| Maximum microwave power in W              | 900             |
| Grill power rating in W                   | 1500            |
| Niche width min. in mm                    | 562             |
| Niche width max. in mm                    | 568             |
| Niche height min. in mm                   | 450             |
| Niche height max. in mm                   | 452             |
| Niche depth in mm                         | 550             |
| Weight in kg                              | 29.1            |
| Ventilation independent of cabinetry      | •               |
| Total rated load in kW                    | 1.6             |
| Voltage in V                              | 220 - 240       |
| Frequency in Hz                           | 50              |
| Fuse rating in A                          | 13              |
| Number of phases                          | 1               |
| Mains cable with plug                     | •               |
| Length of mains connection cable in m     | 2.10            |
| Replacing lamps                           | Service         |
| <b>Accessories included</b>               |                 |
| Grilling rack                             | 1               |
| Gourmet plate                             | 1               |
| Turntable                                 | 1               |

### Available display languages


Available display languages via MultiLingua

? ? ? ? ? ? ? ? , ? ? , ?  
 ? ? ? , deutsch, dansk,  
 english, suomi, français,  
 ελληνικά, italiano, ? ? ? ,  
 ? ? ? , hrvatski, bahasa  
 malaysia, nederlands, norsk,  
 polski, português, română,  
 русский, svenska, srpski,  
 slovenčina, slovenščina,  
 español, čeština, türkçe,  
 українська, magyar


## M 7244 TC

Built-in microwave oven


in a design that is the perfect complement with controls on the top.




M7140TC, M724x, installation drawings



M7140TC, M724xTC, installation drawing




M7140TC, M724xTC, installation drawing  
22 mm – glass, 23.3 mm – stainless steel




M7140TC, M724x, installation drawings

1) Front view, 2) Mains connection cable L=1,600 mm, 3)  
No connection in this area



M7140TC, M724x, installation drawings

1) Front view, 2) Mains connection cable L=1,600 mm, 3)  
No connection in this area



M7140TC, M724x, installation drawings