

DA 7078 D Aura 3.0 White Loom Island cooker hood

special suspension with discreet cables and integrated power supply.



- Ultra-flat and round – unique design with with 70 cm diameter
- Unique user convenience – Con@ctivity
- Sophisticated lighting in a ring – optimum illumination
- Decorative filter design – 10-ply stainless-steel grease filters
- Efficient odour absorption – long-life AirClean filter

A

EAN: 4002516218074 / Material number: 11212640 / Old Material Number: 28707835GB

Construction type	
Island cooker hood	•
Operating modes	
Type of air guide	Recirculation
Design	
Colour	Brilliant white
Customisation possible on request	•
Variable height available as customisation on request	•
User convenience	
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	28.3
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	B
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	14 W
Light intensity in lx	475 lx
Colour temperature in K	3500 Kelvin
Ambient lighting white	•
Fan	
Single-action fan	•
DC motor	•
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	270
Air throughput in Level 2 (m ³ /h) according to EN 61591	360
Air throughput in Level 3 (m ³ /h) according to EN 61591	420
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	615
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	53.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	61.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	65.0

DA 7078 D Aura 3.0 White Loom

Island cooker hood

special suspension with discreet cables and integrated power supply.




EAN: 4002516218074 / Material number: 11212640 / Old Material Number: 28707835GB

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	75.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	47.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	51.0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	61.0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	700
Canopy height in mm	170
Overall height for recirculation in in. (mm)	700
Canopy depth in mm	700
Overall height for recirculation mode cooker hoods in mm	1000
Minimum height above electric hobs in mm	450
Canopy height of round cooker hoods in mm	170
Net weight in kg	22.5
Length of supply lead in m	0.0
Canopy diameter in mm	700
Hard-wired connection	•
Total rated load in kW	0.07
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Fitting template	•
Combination with WiFi-enabled Miele hob	recommended
Optional accessories	
Active charcoal filter	Nein
Active charcoal filter, can be reactivated	DKF 27-R

DA 7078 D Aura 3.0 White Loom

Island cooker hood

special suspension with discreet cables and integrated power supply.



DA7078D – (installation drawings)

1) Cut-out for feeding through the mains cable., The distance to the ceiling or furniture mounted above the unit should be at least 300 mm.