

PDR 908 HP [MAR 1N AC 230V 60Hz]  
Heat-pump dryers  
Lloyd's Register approved, load size 8.0 kg.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218432 / Material number: 11251190 / Old Material Number: 52908288MAR

<b>Construction type and version</b>	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for offshore use	•
Suitable for marine use	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour	2.60
Specific energy consumption in kWh/kg	0.20
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.20
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.17
Programme duration in min.	88
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	88
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	76
<b>Control system</b>	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•
<b>Standard electrical connection</b>	
Heating type	Heat pump
Electrical connection	230V~ 60HZ
Total connected load in kW	1.20
Fuse rating in A	10
Provided with plug	•
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	72.0
Gross weight in kg	78

PDR 908 HP [MAR 1N AC 230V 60Hz]  
 Heat-pump dryers  
 Lloyd's Register approved, load size 8.0 kg.



EAN: 4002516218432 / Material number: 11251190 / Old Material Number: 52908288MAR

Maximum floor load in N	920
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.60
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	95
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.59
Refrigerant global warming potential in kg CO <sub>2</sub> e	1430
Appliance global warming potential in kg CO <sub>2</sub> e	844.00
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
LAN/WiFi module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
Splash-proof safety rating IPX4	•
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•