

PWM 906 [EL DP MAR 3 AC 230V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 6.0 kg.



- Drum volume 57 l, load size 6.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience w. full-touch colour display –M Touch Flex
- 22 % less water consumption and 28 % less energy consumption*
- Thorough cleaning with professional wash programmes

* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516241485 / Material number: 11251370 / Old Material Number: 51906186MAR

| Construction type and version | |
|--|------------------|
| Construction type | Front loader |
| Range | Performance Plus |
| Front | Lotus white |
| Control panel colour | Stainless steel |
| Load in kg | 6.0 |
| Drum volume in l | 57 |
| Door opening [Ø] in mm | 300 |
| Door opening angle in degrees | 167 |
| Door hinge | right |
| Maintenance-free synchronous motor | • |
| Honeycomb drum with perforated drum rear panel | • |
| Application | |
| Suitable for offshore use | • |
| Suitable for marine use | • |
| Performance data | |
| Tested virucidal efficacy | • |
| Proven hygiene | • |
| Specific water consumption for cold water connection in l/kg | 7.50 |
| Specific energy consumption for cold water connection in kWh/kg | 0.16 |
| Specific water consumption for hot water connection in l/kg | 7.00 |
| Specific energy consumption for hot water connection in kWh/kg | 0.06 |
| Water consumption with cold water connection in l | 45.0 |
| Energy consumption with cold water connection in kW | 0.95 |
| Programme duration in minutes with cold water connection | 59 |
| Water consumption with hot water connection in l | 42.0 |
| Energy consumption with hot water connection in kW | 0.38 |
| Programme duration in minutes with cold water and hot water connection | 49 |
| Residual moisture with cold rinse in % | 48 |
| Residual moisture with hot rinse in % | 45 |
| Spin speed in rpm | 1600 |
| g factor | 704 |
| Tested operating hours | 30000 |
| Control system | |
| Control system | M Touch Flex |
| Programmability | programmable |
| Max. delay start in h | 96 |
| Time left display | • |
| Programme sequence indicator | • |
| Language can be selected easily at any time | • |
| Dispensing | |
| Detergent drawer | 3 compartments |
| CapDosing | • |
| Flexible dispensing adapter (optional) | • |
| Maximum number of connections for liquid dispenser pumps [number] | 6 |
| Empty sensor | • |

PWM 906 [EL DP MAR 3 AC 230V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 6.0 kg.



EAN: 4002516241485 / Material number: 11251370 / Old Material Number: 51906186MAR

| Standard electrical connection | |
|--|--------------------------------|
| Heating type | Electric |
| Electrical connection | 3~ 230V 50/60HZ |
| Heater rating in kW | 4.20 |
| Total connected load in kW | 4.40 |
| Fuse rating in A | 16 |
| Water connection/drainage | |
| Cold water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Hot water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Drain pump | DN 22 |
| Dimensions and weight | |
| External dimensions, height in mm | 850 |
| External dimensions, width in mm | 596 |
| External dimensions, depth in mm | 714 |
| External dimensions, gross height in mm | 940 |
| External dimensions, gross width in mm | 660 |
| External dimensions, gross depth in mm | 768 |
| Net weight in kg | 100.0 |
| Gross weight in kg | 104 |
| Maximum floor load in N/m ² | 2820 |
| Emissions data | |
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 1.00 |
| Features | |
| 3-dimensional imbalance monitoring | • |
| Commercial shock absorbers | • |
| Hard-wearing stainless-steel flange | • |
| Disinfection rinse | • |
| EcoSpeed | • |
| Pre-ironing | • |
| Efficient drum rib technology | • |
| Temperature monitoring | • |
| Special heater element | • |
| Automatic load control | • |
| Flow meter | • |
| LED drum lighting, class 1 | • |
| Communication slot | • |
| Add laundry | • |
| Machine-independent accessories | • |
| Efficiency and sustainability | |
| Recycling rate in % | 95 |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| LAN/WiFi module (optional) | • |
| WiFiConn@ct | • |
| Standards, test certificates and symbols | |
| WEEE | • |

PWM 906 [EL DP MAR 3 AC 230V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 6.0 kg.



EAN: 4002516241485 / Material number: 11251370 / Old Material Number: 51906186MAR

Lloyd's Register

Complies with Machinery Directive 2006/42/EC

•
•