

XKM 3200-WL-PLT

Communication module

With LAN and WiFi interface for setting up a connection with external systems.

EAN: 4002516213055 / Material number: 11291940 / Old Material Number: 59320001D



- For integration in a communication slot
- Simple installation

| Product classification | |
|---|---------|
| Washing machines | • |
| Tumble dryers | • |
| Machine/accessory category | |
| PWM 500-08 | • |
| PWM 500-09 | • |
| PWM 506 Mop Star 60 | • |
| PWM 507 | • |
| PWM 508 Mop Star 80 | • |
| PWM 900-09 | • |
| PWM 906 | • |
| PWM 907 | • |
| PWM 908 | • |
| PDR 500-08 | • |
| PDR 507 | • |
| PDR 900-08 | • |
| PDR 908 | • |
| PDW 909 | • |
| PDR 510 | • |
| PDR 910 | • |
| PDR 514 | • |
| PDR 914 | • |
| PDR 518 | • |
| PDR 918 | • |
| PDR 522 | • |
| PDR 922 | • |
| PDR 528 | • |
| PDR 928 | • |
| PDR 544 | • |
| PDR 944 | • |
| Product category | |
| Process documentation/operating documentation/communication | • |
| Product properties | |
| Material | Plastic |
| Colour | Grey |
| Dimensions and weight | |
| External dimensions, net height in mm | 0 |
| External dimensions, net width in mm | 0 |
| External dimensions, net depth in mm | 0 |
| External dimensions, gross height in mm | 55 |
| External dimensions, gross width in mm | 185 |
| External dimensions, gross depth in mm | 230 |
| Net weight [kg] | 0.34 |
| Gross weight in kg | 0.39 |
| Standards, certs, symbols | |
| CE | • |