

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump
Lloyd's Register approved, load size 7.0 kg.



- Drum volume 64 l, load size 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- 22 % less water consumption and 28 % less energy consumption*
- M Select control unit with many standard and special programmes
- Future-proof connectivity via WiFi

* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516264545 / Material number: 11300960 /
Old Material Number: 51507187MAR

| Construction type and version | |
|--|-----------------|
| Construction type | Front loader |
| Range | Performance |
| Front | Lotus white |
| Control panel colour | Stainless steel |
| Load in kg | 7.0 |
| Drum volume in l | 64 |
| Door opening [Ø] in mm | 300 |
| Door opening angle in degrees | 167 |
| Door hinge | right |
| Maintenance-free synchronous motor | • |
| Honeycomb drum with perforated drum rear panel made of stainless steel | • |
| Application | |
| Suitable for offshore use | • |
| Suitable for marine use | • |
| Performance data | |
| Tested virucidal efficacy | • |
| Proven hygiene | • |
| Specific water consumption for cold water connection in l/kg | 7.00 |
| Specific energy consumption for cold water connection in kWh/kg | 0.14 |
| Specific water consumption for hot water connection in l/kg | 6.60 |
| Specific energy consumption for hot water connection in kWh/kg | 0.06 |
| Water consumption with cold water connection in l | 49.0 |
| Energy consumption with cold water connection in kW | 0.98 |
| Programme duration in minutes with cold water connection | 59 |
| Water consumption with hot water connection in l | 46.0 |
| Energy consumption with hot water connection in kW | 0.44 |
| Programme duration in minutes with cold water and hot water connection | 49 |
| Residual moisture with cold rinse in % | 48 |
| Residual moisture with hot rinse in % | 45 |
| Spin speed in rpm | 1600 |
| g factor | 704 |
| Tested operating hours | 30000 |
| Control system | |
| Control system | M Select |
| Programmability | programmable |
| Max. delay start in h | 24 |
| Time left display | • |
| Programme sequence indicator | • |
| Control panel with easy-to-understand symbols | • |
| Language can be selected easily at any time | • |
| Dispensing | |
| Detergent drawer | 3 compartments |

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump
Lloyd's Register approved, load size 7.0 kg.



EAN: 4002516264545 / Material number: 11300960 /
Old Material Number: 51507187MAR

| | |
|---|--------------------------------|
| CapDosing | • |
| Flexible dispensing adapter (optional) | • |
| Maximum number of connections for liquid dispenser pumps [number] | 6 |
| Empty sensor | • |
| Standard electrical connection | |
| Heating type | Electric |
| Electrical connection | 3~ 440V |
| Heater rating in kW | 4.00 |
| Total connected load in kW | 4.20 |
| Fuse rating in A | 10 |
| Possible voltage variant 1 | |
| Electrical connection | 3~ 400V |
| Heater rating in kW | 3.40 |
| Total connected load in kW | 3.60 |
| Fuse rating in A | 10 |
| Possible voltage variant 2 | |
| Electrical connection | 3~ 480V 50/60HZ |
| Heater rating in kW | 4.80 |
| Total connected load in kW | 5.00 |
| Fuse rating in A | 10 |
| Water connection/drainage | |
| Cold water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Hot water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Drain pump | DN 22 |
| Dimensions and weight | |
| External dimensions, height in mm | 850 |
| External dimensions, width in mm | 596 |
| External dimensions, depth in mm | 714 |
| External dimensions, gross height in mm | 944 |
| External dimensions, gross width in mm | 660 |
| External dimensions, gross depth in mm | 768 |
| Net weight in kg | 98.0 |
| Gross weight in kg | 102 |
| Maximum floor load in N | 2820 |
| Emissions data | |
| Emission sound pressure level in the workplace | ≤70 dB(A) re 20 μPa |
| Heat dissipation into the room in MJ/h | 1.00 |
| Features | |
| 3-dimensional imbalance monitoring | • |
| Commercial shock absorbers | • |
| Hard-wearing stainless-steel flange | • |
| Disinfection rinse | • |
| EcoSpeed | • |
| Pre-ironing | • |
| Efficient drum rib technology | • |
| Temperature monitoring | • |

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump
Lloyd's Register approved, load size 7.0 kg.



EAN: 4002516264545 / Material number: 11300960 /
Old Material Number: 51507187MAR

| | |
|--|----|
| Special heater element | • |
| Automatic load control | • |
| Flow meter | • |
| LED drum lighting, class 1 | • |
| Communication slot | • |
| Add laundry | • |
| Machine-independent accessories | • |
| Efficiency and sustainability | |
| Recycling rate in % | 95 |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak-load negotiation / energy management (optional) | • |
| LAN/WiFi module (optional) | • |
| WiFiConn@ct | • |
| Standards, test certificates and symbols | |
| WEEE | • |
| Lloyd's Register | • |
| Complies with Machinery Directive 2006/42/EC | • |