

PW 6080 Vario XL [EL AV 3N AC 400V 50Hz]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain valve.



- Drum volume 80 l, load size 9.0 kg
- Large programme variety – application-specific wash programmes
- Gentle laundry care thanks to the Miele honeycomb drum
- Particularly efficient – low water and energy consumption
- Perfect spinning results – residual moisture 44 %, g-factor 520

\* Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002516235613 / Material number: 11330000 / Old Material Number: 516080X4GB

#### Construction type and version

Construction type	Front loader
Range	Octoplus
Front	Stainless steel
Load ratio	1:9
Load in kg	9.0
Drum volume in l	80
Door opening [Ø] in mm	370
Door opening angle in degrees	180
Door hinge	right
Maintenance-free motor with frequency converter	•
Honeycomb drum	•

#### Application

Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•

#### Performance data

Specific water consumption for hot water connection in l/kg	8.00
Specific energy consumption for hot water connection in kWh/kg	0.05
Programme duration in minutes with cold water connection	57
Programme duration in minutes with cold water and hot water connection	53
Residual moisture with cold rinse in %	49
Residual moisture with hot rinse in %	44
Spin speed in rpm	1300
g factor	520
Tested operating hours	30000

#### Control system

Control system	Profitronic L Vario
Programmability	programmable
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•

PW 6080 Vario XL [EL AV 3N AC 400V 50Hz]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain valve.



EAN: 4002516235613 / Material number: 11330000 / Old Material Number: 516080X4GB

<b>Standard/target grp programmes</b>	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for laundrettes	•
Programmes for residential homes and apartments	•
Programmes for dry cleaners	•
Programmes for commercial laundries	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for universities, nurseries, and school	•
Programmes for hospitals	•
Programmes for fast food restaurants	•
Programmes for camp sites	•
Programmes for sports clubs	•
Programmes for beauty clinics, spas, and fitness studios	•
Programmes for domestic use	•
Programmes for doctors' and dentists' practices	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
Patented liquid dispensing adapter	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	7.95
Total connected load in kW	8.20
Fuse rating in A	16
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Grey water (optional) [number]	1 x 1/2" w/ 3/4" union
Dump valve	DN 70
<b>Dimensions and weight</b>	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	727
External dimensions, gross height in mm	1215
External dimensions, gross width in mm	760
External dimensions, gross depth in mm	820
Net weight in kg	140.0
Gross weight in kg	148
Maximum floor load in N/m <sup>2</sup>	2330
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa

PW 6080 Vario XL [EL AV 3N AC 400V 50Hz]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain valve.



EAN: 4002516235613 / Material number: 11330000 / Old Material Number: 516080X4GB

Heat dissipation into the room in MJ/h 3.00

#### Features

Cloth reprocessing	•
Imbalance monitoring	•
Disinfection rinse	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
Communication slot	•
Machine-independent accessories	•

#### Efficiency and sustainability

Recycling rate in % 95

#### Connection options

Payment system	•
Optical interface for service access	•
Serial interface module RS 232 (optional)	•
Peak load cut-out/energy management (optional)	•

#### Capacities

Respirator masks [number]	4-5
Overalls [number]	1
Over jackets [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Down duvets [number]	1
Down pillows [number]	1-2
Cloths, 22 g [number]	182
Cotton mops, 40 cm / 190 g [number]	42
Cotton mops, 50 cm / 220 g [number]	36
Microfibre mops, 40 cm / 120 g [number]	66
Microfibre mops, 50 cm / 170 g [number]	47
Summer horse blankets [number]	1-2

#### Standards, test certificates and symbols

CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WRAS	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•