

WDD 131 WPS GuideLine

W1 front-loader washing machine:

A | 8 kg | 1400 rpm | operating panel | audible support | audio instructions



- GuideLine – for blind and visually impaired people
- Tested for 20 years of perfect laundry care\*
- Save energy in the best energy efficiency class (A)
- Exclusive CapDosing range for different fabrics and stains\*\*
- Our honeycomb drum ensures that laundry stays in perfect condition

\* During the development phase of the W1 washing machine series, Miele tested models and core components in 5000 wash loads (= 5 wash loads per week for 50 weeks per year) in various programmes. More: [miele.com/20years](http://miele.com/20years)

\*\* Patent EP 2 365 120



EAN: 4002516236894 / Material number: 11331950 / Old Material Number: 11DD1313GB

## Construction type

Suitable for stacking  
Side-by-side  
Slot-in

•  
•  
•  
right

## Model

Product brand  
Front-loader

W1 Chrome Edition  
•

## Spinning

Max. spin speed  
Rinse hold  
Without spin function

1400  
•  
•

## Design

Appliance colour  
Control panel colour  
Door design  
Rotary selector colour  
Control panel version  
Control type  
Display

Lotus white  
Lotus white  
Graphite grey PearlFinish  
Lotus White / Chrome ring  
Slanted  
Rotary control  
DirectSensor yellow,  
7 segment

## Cleaning performance

CapDosing portioned dispensing

•

## Gentle laundry care

Honeycomb drum  
Load in kg

•  
8.0

## User convenience

GuideLine  
Delay start up to 7 hours  
Time left display  
AutoClean detergent drawer

•  
•  
•  
•

## Efficiency and sustainability

Energy efficiency class (A–G)  
Weighted energy consumption per 100 operating cycles for the wash cycle in kWh  
Weighted water consumption per cycle in l  
Spin efficiency class  
Acoustic airborne noise emission class (spin cycle)  
Sound emissions during spin cycle in dB(A) re 1 pW  
Duration of the "ECO 40–60" programme at nominal capacity  
Power rating in off mode in W  
Low temperature wash "Cold" and "20 °C"  
Automatic load control  
Flow meter  
Foam sensing  
ProfiEco motor

A  
47  
47  
B  
A  
70  
219  
0.30  
•  
•  
•  
•  
•

## Wash programmes

Cottons (coloureds)

•

## WDD 131 WPS GuideLine

W1 front-loader washing machine:

A | 8 kg | 1400 rpm | operating panel | audible support | audio instructions




EAN: 4002516236894 / Material number: 11331950 / Old Material Number: 11DD1313GB

Minimum iron	•
Delicates	•
Shirts	•
Woollens (hand-washable)	•
Express 20	•
Dark garments / Denim	•
Outerwear	•
Proofing	•
Cottons Arrow	•
Separate rinse/Starch	•
Drain / Spin	•
ECO 40-60	•
<b>Washing extras</b>	
Short	•
Soak	•
Pre-wash	•
Water plus	•
Additional rinse cycle	•
Buzzer	•
<b>Safety</b>	
Water protection system	Waterproof-System
Safety lock	•
PIN-Code	•
Optical interface	•
<b>Technical data</b>	
Dimensions in mm (width)	596
Dimensions in mm (height)	850
Dimensions in mm (depth)	636
Appliance depth in mm with opened door	1054
Appliance depth excluding door (for building-under) in mm	600
Weight in kg	86
Total rated load in kW	2.10-2.40
Voltage in V	220-240
Fuse rating in A	10
Frequency in Hz	50
Length of water inlet hose in m	1.60
Length of water drain hose in m	1.50
Length of supply lead in m	2


## WDD 131 WPS GuideLine

W1 front-loader washing machine:


A | 8 kg | 1400 rpm | operating panel | audible support | audio instructions




W1 installation drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm