

WED325 WCS PWash&8kg
W1 front-loader washing machine
with QuickPowerWash from 0 to clean in 49 minutes.



- Tested for 20 years of perfect laundry care
- Save energy in the best energy efficiency class (A)
- QuickPowerWash ensures fast, efficient results in just 49 minutes
- The Pre-ironing extra reduces creasing and saves up to 50 % time and effort
- Exclusive CapDosing range for different textiles and stains



EAN: 4002516249382 / Material number: 11358790 / Old Material Number: 11ED3251GB

| Construction type | |
|--|-------------------------------|
| Suitable for stacking | • |
| Side-by-side | • |
| Slot-in | • |
| Can be built-under | • |
| Door hinge | right |
| Model | |
| Product brand | W1 Chrome Edition |
| Front-loader | • |
| Spinning | |
| Max. spin speed | 1400 |
| Rinse hold | • |
| Without spin function | • |
| Design | |
| Appliance colour | Lotus white |
| Control panel colour | Lotus white |
| Door design | Graphite grey PearlFinish |
| Rotary selector colour | Lotus White |
| Control panel version | Straight |
| Control type | Rotary control |
| Display | DirectSensor white, 7 segment |
| Cleaning performance | |
| Innovative PowerWash technology | • |
| CapDosing portioned dispensing | • |
| Gentle laundry care | |
| Honeycomb drum | • |
| Load in kg | 8.0 |
| User convenience | |
| Delay start up to 24 hours | • |
| Time left display | • |
| AutoClean detergent drawer | • |
| AddLoad | • |
| Efficiency and sustainability | |
| Energy efficiency class (A–G) | A |
| Weighted energy consumption per 100 operating cycles for the wash cycle in kWh | 47 |
| Weighted water consumption per cycle in l | 47 |
| Spin efficiency class | B |
| Acoustic airborne noise emission class (spin cycle) | A |
| Sound emissions during spin cycle in dB(A) re 1 pW | 70 |
| Duration of the "ECO 40–60" programme at nominal capacity | 219 |
| Power rating in off mode in W | 0.30 |
| Low temperature wash "Cold" and "20 °C" | • |
| Automatic load control | • |
| Foam sensing | • |
| ProfiEco motor | • |
| Wash programmes | |
| QuickPowerWash | • |
| Cottons (coloureds) | • |


WED325 WCS P Wash&8kg
W1 front-loader washing machine
with QuickPowerWash from 0 to clean in 49 minutes.




EAN: 4002516249382 / Material number: 11358790 / Old Material Number: 11ED3251GB

| | |
|---|---------------------|
| Minimum iron | • |
| Delicates | • |
| Shirts | • |
| Woolens (hand-washable) | • |
| Express 20 | • |
| Proofing | • |
| Cottons Arrow | • |
| Separate rinse/Starch | • |
| Drain / Spin | • |
| ECO 40-60 | • |
| Washing extras | |
| Short | • |
| Pre-wash | • |
| Water plus | • |
| Additional rinse cycle | • |
| Pre-ironing with steam | • |
| Buzzer | • |
| Quality | |
| Counterweights made of cast iron | • |
| Safety | |
| Water protection system | Watercontrol-System |
| Safety lock | • |
| PIN-Code | • |
| Optical interface | • |
| Technical data | |
| Dimensions in mm (width) | 596 |
| Dimensions in mm (height) | 850 |
| Dimensions in mm (depth) | 636 |
| Appliance depth in mm with opened door | 1054 |
| Appliance depth excluding door (for building-under) in mm | 600 |
| Weight in kg | 91 |
| Total rated load in kW | 2.10-2.40 |
| Voltage in V | 220-240 |
| Fuse rating in A | 13 |
| Frequency in Hz | 50 |
| Length of supply lead in m | 2 |


WED325 WCS PWash&8kg
W1 front-loader washing machine
with QuickPowerWash from 0 to clean in 49 minutes.




W1 installation drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm