

PG 8063 [OK Safety]
Free-standing dishwasher
without baskets, for fire brigades.



- Max. cleaning performance: 12 air regulators or 2 baskets/cycle
- Safe reprocessing of air regulators and breathing masks
- Simple to operate thanks to clear fascia panel design
- Safe reprocessing with wash load-specific special programmes
- First-class results thanks to freshwater wash system

EAN: 4002516299530 / Material number: 11459900 / Old Material Number: 61806340GB

Construction type and version	
Construction type	Freestanding dishwasher, front loader
Range	Professional safety
Model	Safety
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Stainless Steel
Side panels	Stainless steel
Application	
Suitable for fire brigades and rescue services	•
Performance data	
Circulation pump Qmax in l/min.	390
Maximum final rinse temperature in °C	60
Cleaning performance air regulators/cycle	12
Cleaning performance breathing masks/cycle	6
Cleaning performance baskets/cycle	2
Service life in wash cycles	15000
Control system	
Control system	TouchControl
Programme selection	Touch on MSetal
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	AC 230V 50HZ
Heater rating in kW	5.50
Total connected load in kW	5.90
Fuse rating in A	30-32
Length of mains connection cable in m	1.70
Possible voltage variant 1	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	8.50
Total connected load in kW	8.90
Fuse rating in A	16
Possible voltage variant 2	
Electrical connection	AC 230V 50HZ
Heater rating in kW	2.50
Total connected load in kW	2.90
Fuse rating in A	13-16
Water connection/drainage	
Cold or hot water [number]	1
Fully/partially demineralised water [number]	1
Required flow pressure in bar	0.40-10.00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•

PG 8063 [OK Safety]
Free-standing dishwasher
without baskets, for fire brigades.



EAN: 4002516299530 / Material number: 11459900 / Old Material Number: 61806340GB

Maximum water hardness in mmol/l	10.70
Water protection system	Waterproof system
Water consumption per wash cycle in l	18.00
Dimensions and weight	
External dimensions, height in mm	820
External dimensions with lid, height in mm	835
External dimensions, net width in mm	600
External dimensions, net depth in mm	600
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Usable space in wash cabinet, height in mm	559
Usable space in wash cabinet, width in mm	530
Usable space in wash cabinet, depth of upper basket	474
Usable space in wash cabinet, depth of lower basket in mm	505
In-feed height above floor in mm	216
Net weight [kg]	72
Gross weight in kg	79
Maximum floor loading in N	1200
Emissions data	
Emissions – sound pressure at workplace	45 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	57.0
Heat dissipation into the room in MJ/h	1.08
Programmes	
Sf Special	•
Sf Special Plus	•
Vario Chem	•
Basket design	
Without baskets	•
Features	
Drying	without
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•
Optical interface	•
A wide range of accessories (optional)	•
Connection options	
External dispensing module for liquid detergent	•
Standards, test certificates and symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
EMC	•
Interference suppression	•
VDE	•
DIN 10512	•
EN 1717	•