

ProCare Tex 70 S - 20 l

Fabric conditioner, liquid concentrate, acidic, 20 l
for care of fibres for long-term fabric touch and feel.



- For use in Miele Professional washing machines
- Ensures a particularly soft finish
- Good antistatic properties in the case of mixed fibre
- Excellent adsorption
- No encapsulated fragrances

EAN: 4002516365525 / Material number: 11520400 / Old Material Number: 59704301DE

Product category	
Washing machines	•
Wash performance	
Antistatic action	Good
Adsorption	Very good
Dispensing	
Adjustment of dispensing concentration possible	•
Suitable for automatic dispensing	•
Manual dispensing	•
Can be used with all degrees of water hardness	•
Dispensing recommendation	
pH value at 20 °C	4,5
How to use	
Launderettes	•
Hotels, catering	•
Cleaning sportswear	•
Cleaning outerwear	•
Cleaning workwear	•
Product properties	
Minimum storage temperature in °C	4
Maximum storage temperature in °C	40
Dimensions and weight	
External dimensions, gross depth in mm	288.00
Product properties	
Medium type	Fabric conditioner
Alkalinity	Acidic
Aggregate form	Liquid concentrate
Composition	Fragrances
Phosphate-free	•
Density (at 20 °C) in g/cm ³	0.99
Free from micro-plastics	•
Ideal additive for all detergents	•
Storage information	
Minimum storage temperature in °C	4
Maximum storage temperature in °C	40
Store in a dry location that is free of frost	•
Containers should always be re-sealed immediately once the required amount of product has been removed	•
Minimum shelf life in months	12
Dimensions and weight	
External dimensions, net height in mm	385
External dimensions, net width in mm	258
External dimensions, net depth in mm	294
External dimensions, gross height in mm	378.00
External dimensions, gross width in mm	256.00
External dimensions, gross depth in mm	288.00
Weight in g	20000
Gross weight in kg	21.00
Fill volume in ml	20000
Compliance, test certificates, and symbols	
GHS/CLP compliant	•