

CM 5410 Silence
Countertop coffee machine
with OneTouch for Two and user profiles for the ultimate in coffee enjoyment.



- Two coffees at once at the touch of a button – OneTouch for Two
- Perfect results and intense coffee flavour – AromaticSystem
- Creamy milk froth for a wide range of coffee specialities
- Convenient cleaning and maintenance programmes
- Convenient when hosting lots of guests – coffee/tea pot function

EAN: 4002516333623 / Material number: 11525230 / Old Material Number: 29541020GB

Construction type and design	
Freestanding bean-to-cup coffee machine	•
Colour	Obsidian black
Convenience features	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
Programmable User profiles	2
Aroma-friendly conical grinder	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
User convenience	
Display	DirectSensor
Multilingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	200
Bean container capacity, total in g	200
Capacity of water container in l	1.3
Drip tray capacity in l	0.8
Easily accessible containers	•
Programmable standby time	•
Programmable settings	•
Beverages	
Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Caffè latte, single	•
Caffè latte, double	•
Hot water, single	•

CM 5410 Silence
Countertop coffee machine
with OneTouch for Two and user profiles for the ultimate in coffee enjoyment.



EAN: 4002516333623 / Material number: 11525230 / Old Material Number: 29541020GB

Coffee pot	•
Efficiency and sustainability	
Energy-saving eco-mode selectable	•
Cleaning convenience	
Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Programmable water hardness	•
Safety	
System lock	•
Technical data	
Height-adjustable serving spout in cm	13.5
Height-adjustable serving spout in cm	8.0
Appliance width in mm	241
Appliance height in mm	360
Appliance depth in mm	460
Total rated load in kW	1.45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Length of supply lead in m	1.2
Accessories supplied	
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•
Available display languages	
Available display languages through MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,