

PRI 421 [G LAM IB]  
 Rotary ironer, gas heated  
 With spring padding and in-feed belt.



- Performance 78.0 kg/h\*, roller diameter 365 mm, working width 2040 mm
- Outstanding finish results thanks to HPC heater plate
- State-of-the-art controls – Touch display
- Selection of the most important settings – favourite programmes
- Perfect rotary ironing performance – flexibly positioned heater plate

\* With 25 % residual moisture – performance data according to DIN 11902: the achievable ironing performance depends on overall conditions such as, for example, the type of laundry and the experience of the operator.

EAN: 4002516367581 / Material number: 11606050 / Old Material Number: 53421112EU

| Construction type and version                              |  |
|--|--|
| Construction type  | Laundry infeed at the front, laundry outfeed at the back |
| Range  | Professional   |
| Outer casing   | Iron grey  |
| Roller diameter in mm                                      | 365  |
| Working width in mm  | 2040   |
| Heater plate material                                      | Aluminium  |
| Padding  | Leaf-spring padding                                      |
| Ironer cover   | ARAMID needle-felt cloth                                 |
| Application  |  |
| Suitable for the hotel and catering industry               | •  |
| Suitable for retirement and care homes                     | •  |
| Suitable for commercial laundries                          | •  |
| Suitable for hospitals                                     | •  |
| Suitable for offshore use                                  | •  |
| Performance data   |  |
| Max. ironing performance at 25 % residual moisture in kg/h | 78.0   |
| Tested operating hours                                     | 20000  |
| Control system   |  |
| Control system   | Touch display  |
| Touch display (optional)                                   | Touch-Display PRI  |
| Programme setting  | Setting of defined programme parameters                  |
| Minimum ironing speed, controlled in m/min                 | 1.5  |
| Maximum ironing speed, controlled in m/min                 | 5.4  |
| Adjustable temperature                                     | Infinitely variable                                      |
| Standard electrical connection                             |  |
| Heating type   | Gas  |
| Electrical connection                                      | 3N AC 400V 50HZ  |
| Electric heater rating in kW                               | 0.00   |
| Gas heater rating in kW                                    | 30.00  |
| Total connected load in kW                                 | 1.00   |
| Fuse rating in A   | 16   |
| Dimensions and weight                                      |  |
| External dimensions, height in mm                          | 1110   |
| External dimensions, width in mm                           | 2759   |
| External dimensions, depth in mm                           | 1441   |
| External dimensions, gross height in mm                    | 1388   |
| External dimensions, gross width in mm                     | 2866   |
| External dimensions, gross depth in mm                     | 1096   |
| Net weight in kg   | 477  |
| Gross weight in kg   | 556  |
| Maximum floor load in N/m <sup>2</sup>                     | 4679   |
| Emissions data   |  |
| Emission sound pressure level in the workplace             | 60 dB(A) re 20 µPa                                       |
| Heat dissipation into the room in MJ/h                     | 15.10  |
| Features   |  |
| Patented EasyFold out-feed table                           | •  |
| Outfeed table extension (optional)                         | •  |

PRI 421 [G LAM IB]  
 Rotary ironer, gas heated  
 With spring padding and in-feed belt.



EAN: 4002516367581 / Material number: 11606050 / Old Material Number: 53421112EU

|  |   |
|--|---|
| HPC heater plate   | • |
| Automatic finger guard   | • |
| FlexControl footswitch   | • |
| In-feed table with feed-in bands   | • |
| Pick-off bands   | • |
| Laundry box  | • |
| Laundry return feed (optional)   | • |
| Cover (optional)   | • |
| Favourite programme  | • |
| Incorrect feed recognition   | • |
| Air suspension   | • |
| Pause function   | • |
| High contact pressure  | • |
| Clean and wax heater plate indicator (op                                 | • |
| Emergency switch-off   | • |
| APRI 319 care set for the heater plate included in the scope of delivery | • |
| Machine-independent accessories  | • |
| <b>Standards, test certificates and symbols</b>                          |   |
| VDE  | • |
| CE   | • |
| DVGW gas   | • |
| WEEE   | • |
| VDE-EMC  | • |
| Splash-proof IPX0  | • |
| UKCA   | • |
| Complies with Machinery Directive 2006/42/EC                             | • |