

K 7433 E

Built-in refrigerator

with DailyFresh, maintenance-free LED lighting, DynaCool and ComfortClean.



- Spacious drawer with moisture control – DailyFresh
- Optimum and maintenance-free LED lighting in compartment
- Uniform temperature distribution inside the appliance – DynaCool
- Dishwasher-proof door shelves – ComfortClean
- More space inside for bulky items – ComfortSize



EAN: 4002516379058 / Material number: 11641270 / Old Material Number: 36743300EU1

<b>Appliance category</b>	
Refrigerator	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Refrigeration section lighting	LED
<b>User convenience</b>	
Networking with Miele@home	•
Freshness system	DailyFresh
ComfortClean	•
DynaCool	•
ComfortSize	•
SoftClose, can be retrofitted	•
<b>Control system</b>	
Operating concept	SensorTouch
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	1
Sabbath mode	•
Party mode	•
Holiday mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	6
Chrome-plated metal bottle rack	•
No. of crisper drawers	1
Number of inner door racks for tinned food	2
Door rack for bottles	2
Door shelves	4
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	105.50
Energy consumption in 24 h in kWh	0.29
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
<b>Technical data</b>	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1397
Niche height in mm max.	1413
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1395
Appliance depth in mm	546

K 7433 E

Built-in refrigerator

with DailyFresh, maintenance-free LED lighting, DynaCool and ComfortClean.




EAN: 4002516379058 / Material number: 11641270 / Old Material Number: 36743300EU1

Weight in kg	45.9
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	21
Climate class	SN-T
Refrigerator compartment in l	236
4* freezer compartment in l	0
Total usable capacity in l	235
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	35
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.2
Replacing lamps	Service
<b>Accessories included</b>	
Egg tray	•

## K 7433 E

### Built-in refrigerator

with DailyFresh, maintenance-free LED lighting, DynaCool and ComfortClean.



K7433E, K7434E, K7464E, K7443D, K7444D, K7473D, K7474D, FNS74470D, installation (footnote\*) (installation drawings)

\*1. View from the front, 2. Mains connection cable, L = 2100 mm, 3. Ventilation cut-out min. 200 cm<sup>2</sup>, 4. Ventilation, 5. No connections permitted in this area

K7433E, K7434E, K7464E, K7443D, K7444D, K7473D, K7474D, FNS7470D, built-in (footnote\*) (installation drawings)

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.

K7433E, K7434E, K7464E, K7443D, K7444D, K7473D, K7474D, FNS7470D, side view (installation drawings)